

**Cable glands
VG EMV PG 16 K18**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Brass cable gland for shielding against interference frequencies with a screening attenuation of up to 100 dB. Contact with cable shield by means of spring washer.

General ordering data

Type	VG EMV PG 16 K18
Order No.	1713880000
Version	cable glands, Brass, nickel-plated, External thread: PG 16
GTIN (EAN)	4008190331351
Qty.	25 pc(s).

Datenblatt

**Cable glands
VG EMV PG 16 K18**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	43 mm	Net weight	77.9 g
--------	-------	------------	--------

General information

AF size 1	30 mm	Cable gland	PG
Clamp insert	TPE	Clamping range, max.	18 mm
Clamping range, min.	14 mm	External thread	PG 16
Length of thread	11 mm	Material	Brass, nickel-plated
O-Ring	NBR	Operating temperature range, max.	135 °C
Operating temperature range, min.	-40 °C	Shield diameter, max.	11.5 mm
Shield diameter, min.	6.5 mm	Torque for cap nut, max.	10 Nm
Torque for cap nut, min.	10 Nm	Torque for connecting adapter, max.	10 Nm
Torque for connecting adapter, min.	10 Nm		

Classifications

ETIM 3.0	EC000441	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-09	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Product information

Descriptive text ordering data	Further versions on request
Descriptive text technical data	Length "L" varies according to cable diameter used

Approvals

Approvals



ROHS	Conform
------	---------