

**Conductor markers  
VT SF 1/12 MC NE WS V0**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

**General ordering data**

|            |                                                                        |
|------------|------------------------------------------------------------------------|
| Type       | VT SF 1/12 MC NE WS V0                                                 |
| Order No.  | <a href="#">1718470001</a>                                             |
| Version    | Conductor markers, MultiCard, 12 x 3.2 mm, Polyamide 66, Colour: White |
| GTIN (EAN) | 4008190349479                                                          |
| Qty.       | 800 pc(s).                                                             |

## Conductor markers VT SF 1/12 MC NE WS V0

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |        |       |        |
|------------|--------|-------|--------|
| Length     | 12 mm  | Width | 3.2 mm |
| Height     | 3.2 mm | Depth | 3.2 mm |
| Net weight | 0.23 g |       |        |

### General data

|                                              |        |                                   |              |
|----------------------------------------------|--------|-----------------------------------|--------------|
| Colour                                       | White  | Material                          | Polyamide 66 |
| Material colour according to resistance code | 9      | Operating temperature range, max. | 120 °C       |
| Operating temperature range, min.            | -50 °C | Size of labelling field           | 12x3.2 mm    |
| Type of printing                             | blank  | UL 94 flammability rating         | V-0          |

### Conductor and cable markers

|                               |                      |                               |                     |
|-------------------------------|----------------------|-------------------------------|---------------------|
| Conductor O.D., max.          | 2.1 mm               | Conductor O.D., min.          | 1.7 mm              |
| Conductor cross-section, max. | 0.75 mm <sup>2</sup> | Conductor cross-section, min. | 0.5 mm <sup>2</sup> |
| Halogen                       | No                   |                               |                     |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-03 |
| eClass 7.1 | 27-14-91-03 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Downloads

|                                 |                                    |
|---------------------------------|------------------------------------|
| M-Print® PRO configuration file | <a href="#">mc_sf_1_12_mcf.zip</a> |
|---------------------------------|------------------------------------|