

**Conductor markers  
CLI T 02-12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



The CLI T sleeve is a high-quality, transparent sleeve for marking conductors and cables with cross-sections up to 75 mm<sup>2</sup>. The CLI T sleeve is available in four lengths so that labelling with long character strings is possible. The transparent sleeve optimally protects the inlay tag against outside influences. The CLI F or TM-I inlay tags are used with this sleeve.

- Wider cross-section range per sleeve
- A special flexible bellow profile ensures a wide application range
- Easy insertion of the TM-I tag into the sleeve pocket before or after connecting the conductor
- Available in five lengths
- Not suitable for labelling with P-Ink or STI pen

**General ordering data**

|            |                                                                         |
|------------|-------------------------------------------------------------------------|
| Type       | CLI T 02-12                                                             |
| Order No.  | <a href="#">1764060000</a>                                              |
| Version    | Conductor markers, 12 x 5 mm, PVC, Colour: Transparent, Conductor O.D.: |
| GTIN (EAN) | 4032248052448                                                           |
| Qty.       | 200 pc(s).                                                              |

**Conductor markers  
CLI T 02-12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technische Daten****Dimensions and weights**

|            |        |       |      |
|------------|--------|-------|------|
| Length     | 12 mm  | Width | 5 mm |
| Height     | 6 mm   | Depth | 6 mm |
| Net weight | 0.13 g |       |      |

**General data**

|                                   |                           |                                   |        |
|-----------------------------------|---------------------------|-----------------------------------|--------|
| Colour                            | Transparent               | Material                          | PVC    |
| Operating temperature range, max. | 80 °C                     | Operating temperature range, min. | -30 °C |
| Recommended industries            | Transportation, Machinery | Type of printing                  | blank  |
| UL 94 flammability rating         | V-0                       |                                   |        |

**Conductor and cable markers**

|                               |                     |                               |                      |
|-------------------------------|---------------------|-------------------------------|----------------------|
| Conductor O.D., max.          | 3 mm                | Conductor O.D., min.          | 1.3 mm               |
| Conductor cross-section, max. | 1.5 mm <sup>2</sup> | Conductor cross-section, min. | 0.22 mm <sup>2</sup> |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|