

Cable glands VG M20 - MS 68

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Screwed joints that comply with the high demands of
class of protection IP 68

General ordering data

Type	VG M20 - MS 68
Order No.	1772220000
Version	cable glands, Brass, nickel-plated, External thread: M 20
GTIN (EAN)	4032248129874
Qty.	50 pc(s).

Cable glands VG M20 - MS 68

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	38 mm	Net weight	28.2 g
--------	-------	------------	--------

General information

AF size 1	22 mm	AF size 2	22 mm
Cable gland	metric	Clamp insert	Polyamide
Clamping range, max.	12 mm	Clamping range, min.	6 mm
External thread	M 20	Length of thread	8 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5	Protection degree with GWDR	IP 68 - 5 bar, IP 69K
Seal insert	CR	Sealing	NBR
Torque for cap nut, max.	9 Nm	Torque for cap nut, min.	7 Nm
Torque for connecting adapter, max.	6 Nm	Torque for connecting adapter, min.	5 Nm

Classifications

ETIM 3.0	EC000441	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-09	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Product information

Descriptive text ordering data	Long-thread version on request VDE for metric version
Descriptive text technical data	Length "L" varies depending on the cable diameter used; IP 69K applies to all metric cable glands; the following thread sizes PG29, PG36, PG42 and PG48 are excluded from IP 69K.

Approvals

Approvals



ROHS	Conform
------	---------