


**Earth terminal  
ZPE 16-2/1AN**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Terminal blocks in tension clamp system and the Z Series are specially customised to the customers' requirements. Less space, spacious labelling area, integrated test point, cross-connection functionality within the Z Series and other Weidmüller terminal lines. Z-Series terminals have a large clamping range and one or two cross-connection slots.

**General ordering data**

Type	ZPE 16-2/1AN
Order No.	<a href="#">1772960000</a>
Version	Earth terminal, PE terminal, Rated cross-section: Tension clamp connection, Wemid, green / yellow
GTIN (EAN)	4032248136599
Qty.	20 pc(s).

## Earth terminal ZPE 16-2/1AN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	65 mm	Width	12 mm
Height	50.5 mm	Height of lowest version	51.5 mm
Net weight	36.5 g		

### Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

### Additional technical data

Explosion-tested version	No	Number of similar terminals	1
Open sides	right	Type of mounting	Snap-on
Version	Tension-clamp connection, With PE connection, One end without connector		

### CSA ratings data

Certificate No. (CSA)	200039-1152892	Wire cross section max. (CSA)	14 AWG
Wire cross section min. (CSA)	26 AWG		

### Clampable wires (additional connection)

Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, min.	1.5 mm <sup>2</sup>	Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max.	16 mm <sup>2</sup>
---	---------------------	---	--------------------

### Clampable wires (rated connection)

Type of connection	Tension clamp connection	Stripping length	18 mm
Blade size	1.0 x 5.5 mm	Connection direction	Inclined / angled
Number of connections	1	Clamping range, rated connection, min.	1.5 mm <sup>2</sup>
Clamping range, rated connection, max.	25 mm <sup>2</sup>	Gauge to IEC 60947-1	A7
Wire connection cross section, solid core, max. rated connection	1.5 mm <sup>2</sup>	Wire connection cross section, solid core max. rated connection	10 mm <sup>2</sup>
Wire connection cross section, stranded, rated connection, min.	16 mm <sup>2</sup>	Wire connection cross section, stranded, rated connection, max.	25 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	16 mm <sup>2</sup>	Wire connection cross-section, finely stranded, min.	1.5 mm <sup>2</sup>
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	1.5 mm <sup>2</sup>	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	16 mm <sup>2</sup>
Cross-section for connected conductor, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, min.	1.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, max.	16 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 14	Wire connection cross section AWG, max.	AWG 4

### Rated data

Rated voltage to adjoining terminal	800 V	Rated impulse withstand voltage to adjacent terminal	8 kV
Standards	IEC 60947-7-2	Pollution severity	3

**Datenblatt**

**Earth terminal  
ZPE 16-2/1AN**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**UL ratings data**

Certificate No. (UR)	E60693	Conductor size Factory wiring max. (UR)	4 AWG
Conductor size Factory wiring min. (UR)	14 AWG	Conductor size Field wiring max. (UR)	4 AWG

**Material data**

Insulating material	Wemid	Material	Wemid
Colour	Yellow, Green	UL 94 flammability rating	V-0

**System specifications**

Product family	Earth terminal	Type of connection	Tension clamp connection
Connection direction	Inclined / angled	Number of levels	1
Number of connections	1	No. of clamping points per level	1
Levels cross-connected internally	No	Mounting rail	TS 35
End cover plate required	Yes		

**Classifications**

ETIM 3.0	EC000901	UNSPSC	30-21-18-11
eClass 5.1	27-14-03-05	eClass 6.2	27-14-03-05
eClass 7.1	27-14-03-05		

**Product information**

Descriptive text technical data	Rated voltage is reduced to 400 V or the IP rated voltage of the distribution terminals.
Descriptive text accessories	The plug-in cross-connections ZQV 2.5/.. , ZQV 4/... and ZQV 6/... can be used.

**Approvals**

Approvals



ROHS Conform