

**Terminal markers  
WS 10/5 MC NE RT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**General ordering data**

|            |                                                                   |
|------------|-------------------------------------------------------------------|
| Type       | WS 10/5 MC NE RT                                                  |
| Order No.  | <a href="#">1773531686</a>                                        |
| Version    | Terminal markers, MultiCard, 10 x 5 mm, Polyamide 66, Colour: Red |
| GTIN (EAN) | 4032248141746                                                     |
| Qty.       | 720 pc(s).                                                        |

## Terminal markers WS 10/5 MC NE RT

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |         |       |      |
|------------|---------|-------|------|
| Length     | 10 mm   | Width | 5 mm |
| Net weight | 0.181 g |       |      |

### General data

|                                              |               |                                   |              |
|----------------------------------------------|---------------|-----------------------------------|--------------|
| Application/manufacturer                     | Allen-Bradley | Colour                            | Red          |
| Colour of printing                           | Black         | Material                          | Polyamide 66 |
| Material colour according to resistance code | 2             | Operating temperature range, max. | 100 °C       |
| Operating temperature range, min.            | -40 °C        | UL 94 flammability rating         | V-2          |

### Connector markers

|                 |      |
|-----------------|------|
| Pitch in mm (P) | 5 mm |
|-----------------|------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000761    | UNSPSC     | 30-21-18-07 |
| eClass 5.1 | 27-14-11-37 | eClass 6.2 | 27-14-11-37 |
| eClass 7.1 | 27-14-11-37 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads


|                                 |                                    |
|---------------------------------|------------------------------------|
| M-Print® PRO configuration file | <a href="#">mc_ws_10_5_mcf.zip</a> |
|---------------------------------|------------------------------------|

### Terminal markers WS 10/5 MC NE RT

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Zeichnungen

### Example of use



### Drawing

