

**Cable markers  
WSM 10 4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**WSM small plates**

- Completely rust-free and acid-resistant
- Embossed characters are still legible when painted
- Also available with custom printing, embossed on a carrier
- Contents of the WSM Service Box, 40 each of: 0-9, A-Ö, +, -, x, /, :, ., ~, =, ü, Earth, Neutral. 200 steel cable ties (200 mm). 30 stainless steel carriers, 48 mm and 60 mm; 20 steel carriers, 84 mm, and 10 steel carriers, 108 mm and 288 mm

**General ordering data**

|            |                                                                     |
|------------|---------------------------------------------------------------------|
| Type       | WSM 10 4                                                            |
| Order No.  | <a href="#">1712500004</a>                                          |
| Version    | Cable markers, 5.5 x 9.9 mm, Stainless steel 1.4404, Colour: Silver |
| GTIN (EAN) | 4008190947224                                                       |
| Qty.       | 200 pc(s).                                                          |

## Cable markers WSM 10 4

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |        |       |        |
|------------|--------|-------|--------|
| Length     | 5.5 mm | Width | 9.9 mm |
| Height     | 0.3 mm | Depth | 0.3 mm |
| Net weight | 0.15 g |       |        |

### General data

|                                   |            |                                   |                        |
|-----------------------------------|------------|-----------------------------------|------------------------|
| Colour                            | Silver     | Material                          | Stainless steel 1.4404 |
| Operating temperature range, max. | 500 °C     | Operating temperature range, min. | -80 °C                 |
| Orientation of print              | horizontal | Printed characters                | Numbers                |
| Printing                          | 4          | Type of printing                  | Standard               |

### Conductor and cable markers

|                               |                     |                               |                    |
|-------------------------------|---------------------|-------------------------------|--------------------|
| Conductor cross-section, max. | 500 mm <sup>2</sup> | Conductor cross-section, min. | 16 mm <sup>2</sup> |
| Halogen                       | No                  |                               |                    |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |