

## Cable markers CLI TM 20-66

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



CLI TM is the right sleeve for large conductor cross-sections. The sleeve's transparent pocket protects the inlay tags against environmental influences. Cable ties are used to fix the transparent CLI TM sleeve in place. Marking is carried out with TM-I 18 for CLI TM 10/33 or ESG 9/17 for CLI TM20/33. Both inlay tags are designed in the proven MultiCard format and can be comfortably labelled with SMark laser, PrintJet, plotter or MC-Mobilo. The CLI F 2/17,5 tag is suitable for CLI TM 20/66.

- Secure attachment with cable ties
- Professional labelling thanks to Weidmüller's marking devices for MultiCards

### General ordering data

Type	CLI TM 20-66
Order No.	<a href="#">1763390000</a>
Version	Cable markers, 66 x 11.3 mm, PVC, Colour: Transparent
GTIN (EAN)	4032248050840
Qty.	50 pc(s).

## Cable markers CLI TM 20-66

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	66 mm	Width	11.3 mm
Height	5 mm	Depth	5 mm
Net weight	1.3 g		

### General data

Colour	Transparent	Material	PVC
Operating temperature range, max.	60 °C	Operating temperature range, min.	-30 °C
Recommended industries	Process, Machinery	Type of printing	blank
UL 94 flammability rating	V-0		

### Conductor and cable markers

Conductor O.D., max.	317 mm	Conductor O.D., min.	10 mm
Conductor cross-section, max.	500 mm <sup>2</sup>	Conductor cross-section, min.	16 mm <sup>2</sup>
Halogen	Yes		

### Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

### Approvals

Approvals	
ROHS	Conform