

Cable markers CLI F 2-17,5 WS/GE NE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The Weidmüller range of conductor and cable marker products provides users with solutions for a wide variety of applications. The field of application ranges from thin conductors to cables with large outside diameters. The product range includes combination systems with individual tags, transparent sleeves and markers which can be fastened with cable ties.

Open and closed markers, as well as printed or blank markers for individual labelling are available. Weidmüller's halogen-free and low-emission conductor markers are in compliance with European standards as well as with the in-house standards of well-known plant manufacturers.

Markers for conductors and cables - Systems are available for:

- Clipping on pre-printed markers to suit individual labelling requirements
- Labelling with characters from a standard character set
- Combining individual, pre-printed characters to form a character code
- Customer labelling with SMark laser, PrintJet, MCP Plus plotter, MC-Mobilo, laser printer (DIN A4 format), thermal transfer printer or STI pen

A selection of samples can be found in the Weidmüller conductor marker sample bag, order No. 1640420000.

General ordering data

Type	CLI F 2-17,5 WS/GE NE
Order No.	1764050000
Version	Cable markers, 17.5 x 9 mm, Polyester, PVC-free, Colour: White
GTIN (EAN)	4032248052431
Qty.	10 pc(s).

Cable markers CLI F 2-17,5 WS/GE NE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	17.5 mm	Width	9 mm
Net weight	26.9 g		

General data

Colour	White	Material	Polyester, PVC-free
Material colour according to resistance code	9	Number per sheet	352
Operating temperature range, max.	120 °C	Operating temperature range, min.	-30 °C
Recommended industries	Process, Machinery	Type of printing	blank
UL 94 flammability rating	HB		

Conductor and cable markers

Conductor O.D., max.	40 mm	Conductor O.D., min.	1 mm
Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	0.22 mm ²
Halogen	Yes		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	lab_cli_f_2_17-5_ws_ge_neutral_mcf.zip
---------------------------------	--