

**Accessories**  
**STB 36.8/IH/GE WTL6/1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

Similar to illustration

**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | STB 36.8/IH/GE WTL6/1      |
| Order No.  | <a href="#">1847760000</a> |
| Version    | Accessories, Socket        |
| GTIN (EAN) | 4032248379170              |
| Qty.       | 50 pc(s).                  |

## Accessories

### STB 36.8/IH/GE WTL6/1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 6 mm    | Width (inches)  | 0.236 inch |
| Height     | 36.8 mm | Height (inches) | 1.449 inch |
| Depth      | 39.8 mm | Depth (inches)  | 1.567 inch |
| Net weight | 1.188 g |                 |            |

### Temperatures

|                                   |        |                                  |        |
|-----------------------------------|--------|----------------------------------|--------|
| Operating temperature range, max. | 100 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max.  | 100 °C |                                  |        |

### Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

### Material data

|                           |              |        |        |
|---------------------------|--------------|--------|--------|
| Material                  | Polyamide 66 | Colour | yellow |
| UL 94 flammability rating | V-2          |        |        |

### System specifications

|         |                   |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

### Additional technical data

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No              | Installation advice | Direct mounting |
| Type of fixing           | when screwed in | Type of mounting    | when screwed in |

### Dimensions

|               |         |              |         |
|---------------|---------|--------------|---------|
| Plug-in depth | 11.1 mm | TS 35 offset | 45.5 mm |
|---------------|---------|--------------|---------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001134    | ETIM 4.0   | EC001134    |
| ETIM 5.0   | EC001134    | ETIM 6.0   | EC002848    |
| UNSPSC     | 30-21-18-11 | eClass 5.1 | 27-14-11-45 |
| eClass 6.2 | 27-14-92-14 | eClass 7.1 | 27-14-92-14 |
| eClass 8.1 | 27-14-92-14 | eClass 9.0 | 27-14-11-92 |
| eClass 9.1 | 27-14-11-92 |            |             |

### Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |                                     |
|--------------------|-------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 1 TERM 16/17 EN</a> |
| Engineering Data   | <a href="#">STEP</a>                |

Creation date May 28, 2019 10:59:56 AM CEST