

**VG K (standard plastic cable gland)
VG M20-1/K68****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Screwed joints that comply with the high demands of
class of protection IP 68

General ordering data

Type	VG M20-1/K68
Order No.	1772300000
Version	VG K (standard plastic cable gland), Cable glands, M 20, 10 mm, OD min. 6 - OD max. 12 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
GTIN (EAN)	4032248129966
Qty.	50 pc(s).

VG K (standard plastic cable gland) VG M20-1/K68

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	39.5 mm	Length (inches)	1.555 inch
Net weight	10.3 g		

General information

AF size 1	24 mm	Cable glands	metric
External thread	M 20	Length of thread	10 mm
Material		Note: protection class	IP66 applications only possible with sealing ring for threaded connections. Without sealing ring for threaded connections, only IP54 is possible.
	Polyamide 6		
Operating temperature range, max.	100 °C	Operating temperature range, min.	-30 °C
Outer cable diameter, max.	12 mm	Outer cable diameter, min.	6 mm
Pitch of thread	1.5 mm	Protection degree	IP67, IP68 - 5 bar (30 min.)
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Seal insert	CR
Standards	DIN EN 62444, EN 62444, IEC 62444	Torque for cap nut, max.	6 Nm
Torque for cap nut, min.	5 Nm	Torque for connecting adapter, max.	6 Nm
Torque for connecting adapter, min.	5 Nm	Torque for lock nut, max.	6 Nm
Torque for lock nut, min.	5 Nm	UL 94 flammability rating	V-2

Classifications

ETIM 3.0	EC000441	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000441
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-09
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09
eClass 8.1	27-14-91-09	eClass 9.0	27-14-44-32
eClass 9.1	27-14-44-32		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP STEP