

Cable glands VG M40 - K 68

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Screwed joints that comply with the high demands of
class of protection IP 68

General ordering data

Type	VG M40 - K 68
Order No.	1772330000
Version	cable glands, Polyamide 6, RAL 7035, External thread: M 40
GTIN (EAN)	4032248129997
Qty.	10 pc(s).

Cable glands VG M40 - K 68

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	69.9 mm	Net weight	76 g
--------	---------	------------	------

General information

AF size 1	53 mm	Cable gland	metric
Clamping range, max.	32 mm	Clamping range, min.	22 mm
Colour code	RAL 7035	DIN	EN 50262 (for M thread)
External thread	M 40	Length of thread	18 mm
Material	Polyamide 6	Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C	Pitch of thread	1.5
Seal insert	CR	Torque for cap nut, max.	19 Nm
Torque for cap nut, min.	16 Nm	Torque for connecting adapter, max.	12 Nm
Torque for connecting adapter, min.	7 Nm	UL 94 flammability rating	V-2

Classifications

ETIM 3.0	EC000441	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-09	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Product information

Descriptive text ordering data	Long-thread version on request, halogen-free without sealing ring
Descriptive text technical data	Version with moulded sealing lip Length L varies depending on the cable diameter used.

Approvals

Approvals



ROHS	Conform
------	---------