

**Conductor markers
TM 0/18 TWIN HF/HB**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



TM/HF Twin double-sided labelling: 0.22 – 2.5 mm.
Twin sleeves enable double-sided marking of a conductor.
The sleeves can hold two TM-I 18 tags so that, for example, the input and output designations of a cable can be read at one position. The transparent, halogen-free sleeves can be used on conductors with an outside diameter of 1.3 to 4.0 mm.

General ordering data

Type	TM 0/18 TWIN HF/HB
Order No.	1891810000
Version	Conductor markers, 18 x 5 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.:
GTIN (EAN)	4032248504558
Qty.	500 pc(s).

Conductor markers TM 0/18 TWIN HF/HB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	18 mm	Width	5 mm
Height	10 mm	Net weight	0.278 g

General data

Colour	Transparent	Material	Polyethylene LD
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Recommended industries	Transportation, Machinery	Type of printing	blank
UL 94 flammability rating	HB		

Conductor and cable markers

Conductor O.D., max.	2.6 mm	Conductor O.D., min.	1.3 mm
Conductor cross-section, max.	1.5 mm ²	Conductor cross-section, min.	0.22 mm ²
Halogen	No		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-03
eClass 7.1	27-14-91-03		

Approvals

Approvals	
ROHS	Conform