

**W-Series
WPE 95N/120N**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The PE terminals are available in two designs: standard and compact (N), with rated cross-section from 1.5 mm² to 150 mm² (e.g. 2.5 mm² – WPE 2.5 or 4 mm² – WPE 4N).

General ordering data

Type	WPE 95N/120N
Order No.	1846030000
Version	W-Series, PE terminal, Rated cross-section: 95 mm ² , Screw connection, Direct mounting
GTIN (EAN)	4032248394531
Qty.	5 pc(s).

W-Series WPE 95N/120N

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	91 mm	Width	27 mm
Height	90 mm	Height of lowest version	91 mm
Net weight	335.987 g		

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Rated data IECEx/ATEX

Certificate No. (ATEX)	KEMA98ATEX1683U	ATEX certificate	KEMA98ATEX1683U_d.pdf
ATEX certificate	KEMA98ATEX1683U_e.pdf	Wire cross section max. (ATEX)	120 mm ²
Voltage, cross-connection		Operating temperature range	For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity
	CrossConnectionGuide.pdf		
Marking EN 60079-7	Ex e II	Marking ATEX Directive 94/9/EC	II 2 G D

Additional technical data

Explosion-tested version	Yes	Installation advice	Direct mounting
Number of similar terminals	1	Open sides	closed
Type of mounting	Snap-on	Version	Screw connection, With PE connection, closed

CSA ratings data

Certificate No. (CSA)	200039-1057876	Wire cross section max. (CSA)	0000 AWG
Wire cross section min. (CSA)	4 AWG		

Clampable wires (rated connection)

Type of connection	Screw connection	Stripping length	27 mm
Blade size	S6 (DIN 6911)	Connection direction	on side
Clamping range, rated connection, min.	16 mm ²	Clamping range, rated connection, max.	150 mm ²
Clamping screw	M 10	Tightening torque, min.	12 Nm
Tightening torque, max.	20 Nm	Gauge to IEC 60947-1	B13
Wire connection cross section, solid core, max. rated connection	16 mm ²	Wire connection cross section, solid core max. rated connection	16 mm ²
Wire connection cross section, stranded, rated connection, min.	16 mm ²	Wire connection cross section, stranded, rated connection, max.	150 mm ²
Wire connection cross section, finely stranded, max.	120 mm ²	Wire connection cross-section, finely stranded, min.	16 mm ²
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	16 mm ²	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	95 mm ²

Rated data

Rated cross-section	95 mm ²	Rated voltage to adjoining terminal	1,000 V
Rated impulse withstand voltage to adjacent terminal	8 kV	Standards	IEC 60947-7-2
Pollution severity	3		

W-Series WPE 95N/120N

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

UL ratings data

Certificate No. (cURus)	E60693	Conductor size Factory wiring max. (cURus)	000 AWG
Conductor size Factory wiring min. (cURus)	4 AWG	Conductor size Field wiring max. (cURus)	000 AWG
Conductor size Field wiring min. (cURus)	4 AWG		

Material data

Material	Wemid	Colour	Yellow, Green
UL 94 flammability rating	V-0		

System specifications

Product family	W-Series	Type of connection	Screw connection
Connection direction	on side	Number of levels	1
No. of clamping points per level	2	Levels cross-connected internally	No
End cover plate required	No		

Classifications

ETIM 3.0	EC000901	UNSPSC	30-21-18-11
eClass 5.1	27-14-03-05	eClass 6.2	27-14-03-05
eClass 7.1	27-14-03-05		

Product information

Descriptive text ordering data	UL, CSA and ATEX certifications are pending
Descriptive text technical data	For 50 - 150 mm ² , the TS 35 x 15 (copper, 2.3 mm thick) mounting rail should be used.
Descriptive text accessories	Rail support protective insulation for installation of mounting rail "SH 2" order No. 0494920000 (QTY 10).

Approvals

Approvals



ROHS Conform

W-Series WPE 95N/120N

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

