

**W-Series, Accessories
WTA 8 KO-TN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.

Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	WTA 8 KO-TN
Order No.	1915480000
Version	W-Series, Accessories, Test adapter
GTIN (EAN)	4032248548057
Qty.	25 pc(s).

W-Series, Accessories WTA 8 KO-TN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	39 mm	Width	6 mm
Height of lowest version	78 mm	Net weight	8.08 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Clampable wires (additional connection)

Clamping range, further connection, max.	1.5 mm ²	Rated cross-section, further connection	1.5 mm ²
--	---------------------	---	---------------------

Clampable wires (rated connection)

Wire connection cross section, solid core, max. rated connection	0.5 mm ²	Wire connection cross section, solid core max. rated connection	2.5 mm ²
--	---------------------	---	---------------------

Rated data

Rated cross-section	1.5 mm ²	Rated voltage	205 V
Rated current	6 A		

Material data

Material	PA 66	Colour	Black
UL 94 flammability rating	V-2		

System specifications

Product family	W-Series, Accessories
----------------	-----------------------

Classifications

ETIM 3.0	EC002255	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-45	eClass 6.2	27-14-92-14
eClass 7.1	27-14-92-14		

Product information

Descriptive text technical data	Rated current 6 A
---------------------------------	-------------------

Approvals

Approvals



ROHS	Conform
------	---------