

# MSDS Report

Report No.: MTi171013M002

Date of issue: Oct. 26, 2017

Sample Name: Li-ion Battery

---

Model(s): 442839

---

Applicant: SHENZHEN TOP ENERGY Co., Ltd.

---

Address: Room 101、201、301, A building, Miao Jiao Ling Tongfu  
Industrial district , Yan' an Road NO.11 North, Gaoyuan  
Community, Kuichong Street, Dapeng District, Shenzhen, CHINA

---

Shenzhen Microtest Co., Ltd.

<http://www.mtitest.com>



Tested by (printed name and signature) .....	Roy Qin	<i>Roy Qin</i>
Reviewed by (printed name and signature) .....	Iric Yang	<i>Iric Yang</i>
Approved by (printed name and signature) .....	Tom Xue	<i>Tom Xue</i>
<b>Testing laboratory.....</b>	<b>Shenzhen Microtest Co., Ltd.</b>	
Address .....	No.102A & 302A, East Block, Hengfang Industrial Park, Xingye Road, Xixiang, Bao'an District, Shenzhen, Guangdong, China	
Tested Date.....	2017-10-14 to 2017-10-26	

## Material Safety Data Sheet

### Section 1- Chemical Product and Company Identification

Product Name.....	Li-ion Battery
Trade Mark.....	N/A
Model .....	442839
Nominal Voltage .....	3.7V
Rated Capacity .....	450mAh,1.665Wh
Weight.....	About 9.0 g
Dimension.....	T:4.4mm, W:28.0 mm H: 40.0mm
<b>Manufacture's Name.....</b>	<b>SHENZHEN TOP ENERGY Co., Ltd.</b>
Address.....	Room 101、201、301, A building, Miao Jiao Ling Tongfu Industrial district , Yan' an Road NO.11 North, Gaoyuan Community, Kuichong Street, Dapeng District, Shenzhen, CHINA
Contact information.....	Tel:+86-13798312791
E-mail address.....	418810652@qq.com
Version number .....	V1.0
Referenced documents.....	ISO 11014:2009 Safety data sheet for chemical products

## Section 2 – Hazards Identification

Preparation hazards and classification	Not dangerous with normal use. Do not dismantle, open or shred Li-ion Battery . Exposure to the ingredients contained within or their ingredients products could be harmful.
Appearance, Color, and Odor	Solid object with no odor, silvery.
Primary Route(s) of Exposure	These chemicals are contained in a sealed stainless steel enclosure. Risk of exposure occurs only if the cell is mechanically, thermally or electrically abused to the point of compromising the enclosure. If this occurs, exposure to the electrolyte solution contained within can occur by Inhalation, Ingestion, Eye contact and Skin contact
Potential Health Effects	<p><b>ACUTE (short term):</b> see Section 8 for exposure controls In the event that this battery has been ruptured, the electrolyte solution contained within the battery would be corrosive and can cause burns.</p> <p><b>Inhalation:</b> Inhalation of materials from a sealed battery is not an expected route of exposure. Vapors or mists from a ruptured battery may cause respiratory irritation.</p> <p><b>Ingestion:</b> Swallowing of materials from a sealed battery is not an expected route of exposure. Swallowing the contents of an open battery can cause serious chemical burns of mouth, esophagus, and gastrointestinal tract.</p> <p><b>Skin:</b> Contact between the battery and skin will not cause any harm. Skin contact with contents of an open battery can cause severe irritation or burns to the skin.</p> <p><b>Eye:</b> Contact between the battery and the eye will not cause any harm. Eye contact with contents of an open battery can cause severe irritation or burns to the eye.</p> <p><b>CHRONIC (long term):</b> see Section 11 for additional toxicological data</p>
Medical Conditions Aggravated by Exposure	Not applicable
Reported as carcinogen	Not applicable

### Section 3 – Composition/Information on Ingredients

Li-ion Battery is a mixture.

Hazardous Ingredients (Chemical Name)	Concentration or concentration ranges( % )	CAS Number
Lithium Cobalt Oxides(LiCoO <sub>2</sub> )	29.73	12190-79-3
Graphite(C)	21.47	7782-42-5
Electrclyte	14.28	/
Copper Foils	9.62	7440-50-8
Aluminum foil	7.30	7429-90-5
Polyvinylidene Fluoride	3.61	24937-79-9
SBR(C <sub>8</sub> H <sub>8</sub> C <sub>4</sub> H <sub>6</sub> )	1.52	9003-55-8
Polyethylene(PE)	2.53	90989-93-8
Nickel	1.66	61788-71-4
Aluminum packing Foil	6.17	12042-91-0
Other	2.11	/

Labeling according to EC directives.

No symbol and risk phrase are required.

Note:CAS number is Chemical Abstract Service Registry Number.

N/A=Not apply

### Section 4 – First-aid Measures

<b>Inhalation</b>	If contents of an opened battery are inhaled, remove source of contamination or move victim to fresh air. Obtain medical advice.
<b>Skin contact</b>	If skin contact with contents of an open battery occurs, as quickly as possible remove contaminated clothing, shoes and leather goods. Immediately flush with lukewarm, gently flowing water for at least 30 minutes. If irritation or pain persists, seek medical attention. Completely decontaminate clothing, shoes and leather goods before reuse or discard.
<b>Eye contact</b>	If eye contact with contents of an open battery occurs, immediately flush the contaminated eye(s) with lukewarm, gently flowing water for at least 30 minutes while holding the eyelids open. Neutral saline solution may be used as soon as it is available. If necessary, continue flushing during transport to emergency care facility. Take care not to rinse contaminated water into the unaffected eye or onto face. Quickly transport victim to an emergency care facility.
<b>Ingestion</b>	If ingestion of contents of an open battery occurs, never give anything by mouth if victim is rapidly losing consciousness, or is unconscious or convulsing. Have victim rinse mouth thoroughly with water. DO NOT INDUCE VOMITING. Have victim drink 60 to 240 mL (2-8 oz.) of water. If vomiting occurs naturally, have victim lean

	forward to reduce risk of aspiration. Have victim rinse mouth with water again. Quickly transport victim to an emergency care facility.
--	--

### Section 5 – Fire-fighting Measures

Flammable Properties	In the event that this battery has been ruptured, the electrolyte solution contain within the battery would be flammable. Like any sealed container, battery cells may rupture when exposed to excessive heat; this could result in the release of flammable or corrosive materials.
Suitable extinguishing Media	Use extinguishing media suitable for the materials that are burning.
Unsuitable extinguishing Media	Not available
Explosion Data	<b>Sensitivity to Mechanical Impact:</b> This may result in rupture in extreme cases <b>Sensitivity to Static Discharge:</b> Not Applicable
Specific Hazards arising from the chemical	Fires involving Li-ion Battery can be controlled with water. When water is used, however, hydrogen gas may evolve. In a confined space, hydrogen gas can form an explosive mixture. In this situation, smothering agents are recommended to extinguish the fire
Protective Equipment and precautions for firefighters	As for any fire, evacuate the area and fight the fire from a safe distance. Wear a pressure-demand, self-contained breathing apparatus and full protective gear. Fight fire from a protected location or a safe distance. Use NIOSH/MSHA approved full-face self-contained breathing apparatus (SCBA) with full protective gear.
NFPA	Health: 0 Flammability: 0 Instability: 0

### Section 6 – Accidental Release Measures

Personal Precautions, protective equipment, and emergency procedures	Restrict access to area until completion of clean-up. Do not touch the spilled material. Wear adequate personal protective equipment as indicated in Section 8.
Environmental Precautions	Prevent material from contaminating soil and from entering sewers or waterways.
Methods and materials for Containment	Stop the leak if safe to do so. Contain the spilled liquid with dry sand or earth. Clean up spills immediately.
Methods and materials for cleaning up	Absorb spilled material with an inert absorbent (dry sand or earth). Scoop contaminated absorbent into an acceptable waste container. Collect all contaminated absorbent and dispose of according to directions in Section 13. Scrub the area with detergent and water;

	collect all contaminated wash water for proper disposal.
--	--

### Section 7 – Handling and Storage

Handling	<p>Don't handling Li-ion Battery with metalwork. Do not open, disassemble, crush or burn battery. Ensure good ventilation/ exhaust at the workplace.</p> <p>Prevent formation of dust.</p> <p>Information about protection against explosions and fires: Keep ignition sources away- Do not smoke.</p>
Storage	<p>If the Li-ion Battery are subject to storage for such a long term as more than 6 months, it is recommended to recharge the Li-ion Battery periodically.</p> <p>Storage Temperature</p> <p>Short period less than 3 months: -10°C ~+40°C</p> <p>Humidity: 60±25%RH</p> <p>Do not storage Li-ion Battery haphazardly in a box or drawer where they may short-circuit each other or be short-circuited by other metal objects.</p> <p>Do not expose Li-ion Battery on heat or fire. Avoid storage in direct sunlight. Do not store together with oxidizing and acidic materials. Do not store together with oxidizing and acidic materials. Keep container tightly sealed.</p>

### Section 8 – Exposure Controls and Personal Protection

Engineering Controls	<p>Use local exhaust ventilation or other engineering controls to control sources of dust, mist, fumes and vapor.</p> <p>Keep away from heat and open flame. Store in a cool, dry place.</p>
Personal Protective Equipment	<p><b>Respiratory Protection:</b> Not necessary under normal conditions.</p> <p><b>Skin and body Protection:</b> Not necessary under normal conditions, Wear neoprene or nitrile rubber gloves if handling an open or leaking battery.</p> <p><b>Hand protection:</b> Wear neoprene or natural rubber material gloves if handling an open or leaking battery.</p> <p><b>Eye Protection:</b> Not necessary under normal conditions, Wear safety glasses if handling an open or leaking battery.</p>
Other Protective Equipment	<p>Have a safety shower and eye wash fountain readily available in the immediate work area.</p>
Hygiene Measures	<p>Do not eat, drink, or smoke in work area. Maintain good housekeeping.</p>

## Section 9 – Physical and Chemical Properties

Physical State	Form: Solid
	Color: Silvery
	Odour: Monotony
Change in condition:	
pH, with indication of the concentration	Not applicable
Melting point/freezing point	Not available.
Boiling Point, initial boiling point and Boiling range:	Not available.
Flash Point	Not available.
Upper/lower flammability or explosive limits	Not available.
Vapor Pressure:	Not applicable
Vapor Density: (Air = 1)	Not applicable
Density/relative density	Not available.
Solubility in Water:	Insoluble
n-octanol/water partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Odour threshold	Not available.
Evaporation rate	Not available.
Flammability (soil, gas)	Not available.
Viscosity	Not applicable

## Section 10 – Stability and Reactivity

Stability	The product is stable under normal conditions.
Conditions to Avoid (e.g. static discharge, shock or vibration)	Do not subject Li-ion Battery to mechanical shock. Vibration encountered during transportation does not cause leakage, fire or explosion. Do not disassemble, crush, short or install with incorrect polarity. Avoid mechanical or electrical abuse.

Incompatible Materials	Not Available
Hazardous Decomposition Products	This material may release toxic fumes if burned or exposed to fire
Possibility of Hazardous Reaction	Not Available

## Section 11 – Toxicological Information

Irritation	Risk of irritation occurs only if the cell is mechanically, thermally or electrically abused to the point of compromising the enclosure. If this occurs, irritation to the skin, eyes and respiratory tract may occur.
Sensitization	Not Available
Neurological Effects	Not Available
Teratogenicity	Not Available
Reproductive Toxicity	Not Available
Mutagenicity (Genetic Effects)	Not Available
Toxicologically Synergistic Materials	Not Available

## Section 12 – Ecological Information

General note:	Water hazard class 1(Self-assessment): slightly hazardous for water. Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
Anticipated behavior of a chemical product in environment/possible environmental impact/ecotoxicity	Not Available
Mobility in soil	Not Available
Persistence and Degradability	Not Available
Bioaccumulation potential	Not Available
Other Adverse Effects	Not Available



### **Section 13 – Disposal Considerations**

Product disposal recommendation: Observe local, state and federal laws and regulations.

Packaging disposal recommendation: Be aware discarded batteries may cause fire, tape the battery terminals to insulate them. Don't disassembly the battery. Completely discharge containers(no tear drops, no powder rest, scraped carefully). Containers may be recycled or re-used. Observe local, state and federal laws and regulations.

### **Section 14 – Transport Information**

For the international transport of lithium batteries, they must comply with these regulations: the International Maritime Dangerous Goods (IMDG) Code by International Maritime Organization (IMO), Dangerous Goods Regulations (DGR) by International Air Transport Association (IATA) and Technical Instructions for the Safe Transport of Dangerous Goods by Air by International Civil Aviation Organization (ICAO). These regulations are based on the UN Recommendations on the Transport of Dangerous Goods, Manual of Tests and Criteria.

Lithium batteries which meet the requirements of UN38.3 (UN Manual of Tests and Criteria, Part III, subsection 38.3) could be transported by air and by sea as ordinary goods, otherwise should be transported according to Class 9, Packing Group II hazardous goods.

1. For Lithium battery, UN 3480 or UN 3481. Lithium ion batteries or Lithium ion batteries contained in equipment or Lithium ion batteries packed with equipment.
2. The consignment should be fully described by proper shipping name and packed, marked and in proper condition for carriage by air. The consignment is not classified as dangerous under the current edition of the IATA 58th Effective, Dangerous goods regulation and all applicable carrier and government regulations. The product meets the requirements in IMDG CODE (Amdt.38-16) Special provision 188, it can be transported by sea under this Special provision.
3. For transported by air, Lithium-ion Cells/Batteries shipped as "Not Restricted" Cargo must comply with Section II/Section IB of PI965 or Section II of P966-PI967 accordingly; For cells, the Watt-hour rating should not be more than 20Wh; For batteries, the Watt-hour rating should not be more than 100Wh. Watt-hour rating must be marked on the outside of the battery case (marked by manufacturer).
4. Each consignment must be accompanied with a document such as an air waybill with an indication. For those Lithium ion cells/ batteries contained in equipment, the equipment must be equipped with an effective means of preventing accidental activation. The telephone number for additional information for SHENZHEN TOP ENERGY Co., Ltd. is +86-13798312791.
5. Quantity per package shall not exceed 10kg in Section IB of PI965. Quantity per package shall not exceed 5kg in Section II of PI966-PI967.
6. For only lithium battery transparent or lithium battery packed with equipment transparent, each package must be capable of withstanding a 1.2m drop test in any orientation without damage of cells or batteries contained therein.
7. Li-ion Battery which meet the requirements of 442839 could be transported by air and by sea, and the batteries manufactured by SHENZHEN TOP ENERGY Co., Ltd. meet these requirements. (442839 Li-ion Battery identified by the manufacturer as being defective for safety reasons or that have been damaged, that have the potential of producing a dangerous evolution of heat, fire or short circuit are forbidden for transport.)
8. Cells and batteries must be protected so as to prevent short circuits. This includes protection against contact with conductive materials within the same packaging that could lead to short circuit.

### Section 15 – Regulatory Information

OSHA hazard communication standard (29 CFR 1910.1200)

\_\_\_\_\_ Hazardous

\_\_\_\_\_√\_\_\_\_\_ Non-hazardous

### Section 16 – Other Information

The information above is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. We makes no warranty of merchantability or any other warranty, express or implied, with respect to such information, and we assume no liability resulting from its use. Users should make their own investigations to determine the suitability of the information for their particular purposes. In no way shall we be liable for Any claims, losses, or damages of any third party or for lost profits or any special, indirect, incidental, consequential or exemplary damages, however arising from using the above information.

The data/information contained herein has been reviewed and approved for general release on the basis that this document contains no export controlled information.

\*\*\*\*\* End of Report \*\*\*\*\*