

**Z-series, Accessories
STGH O.ZA ZRV2.5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



One terminal strip for the functional unit, one plug-in connector for the cable loom fabrication. All that remains to be done is to clip the two units together during final assembly – just like a plug-in connector. Finished! Whether for railway engineering, mechanical engineering or shipbuilding applications, all are served excellently by the products of the Weidmüller Z-Series. This is because the products are easy to use and practical, and the connections are simple, reliable and quick. Modular and flexible connection systems are especially in demand where complete functional units have to be prefabricated or replaced.

General ordering data

Type	STGH O.ZA ZRV2.5
Order No.	1907010000
Version	Z-series, Accessories, Multi-tier modular terminal, 5.15 mm, Dark Beige, Wemid, Dark Beige, Direct mounting
GTIN (EAN)	4032248530779
Qty.	50 pc(s).

Z-series, Accessories STGH 0.ZA ZRV2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	31.5 mm	Width	5.15 mm
Height	24.2 mm	Net weight	1.799 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Installation advice	Direct mounting	Version	Housing base part
---------------------	-----------------	---------	-------------------

Clampable wires (rated connection)

Type of connection	Plug-in connection
--------------------	--------------------

Rated data

Rated cross-section	2.5 mm ²
---------------------	---------------------

Material data

Insulating material	Wemid	Material	Wemid
Colour	Dark Beige	UL 94 flammability rating	V-0

System specifications

Product family	Z-series, Accessories	Type of connection	Plug-in connection
----------------	-----------------------	--------------------	--------------------

Classifications

ETIM 3.0	EC000897	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-18	eClass 6.2	27-14-11-20
eClass 7.1	27-14-11-20		

Approvals

Approvals



ROHS	Conform
------	---------