

Z-series, Accessories
ZQV 2.5/20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



A plug-in cross-connection system (ZQV) is available for all modular terminals of the P-series.

General ordering data

| | |
|------------|---|
| Type | ZQV 2.5/20 |
| Order No. | 1908960000 |
| Version | Z-series, Accessories, Cross-connector, For the terminals, No. of poles: 20 |
| GTIN (EAN) | 4032248535293 |
| Qty. | 20 pc(s). |

Datenblatt

**Z-series, Accessories
ZQV 2.5/20**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|--------|----------|------------|----------|
| Length | 100.3 mm | Width | 2.8 mm |
| Height | 27.6 mm | Net weight | 13.785 g |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Operating temperature | | Storage temperature | |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

Additional technical data

| | | | |
|---------------------|-----------------|---------|-------------------|
| Installation advice | Direct mounting | Version | For the terminals |
|---------------------|-----------------|---------|-------------------|

Material data

| | | | |
|---------------------------|-------|--------|--------|
| Material | Wemid | Colour | Yellow |
| UL 94 flammability rating | V-0 | | |


System specifications

| | |
|----------------|-----------------------|
| Product family | Z-series, Accessories |
|----------------|-----------------------|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000489 | UNSPSC | 30-21-18-01 |
| eClass 5.1 | 27-14-11-40 | eClass 6.2 | 27-14-11-40 |
| eClass 7.1 | 27-14-11-40 | | |

Approvals

| | |
|-----------|---|
| Approvals |  |
| ROHS | Conform |