VG K (standard plastic cable gland)
VG M32-K67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Cable glands for professional use in industrial applications which meet the highest demands in terms of quality and safety. They are available made from polyamide, polystyrene and brass.

General ordering data

Type	VG M32-K67
Order No.	1909720000
Version	VG K (standard plastic cable gland), Cable glands, M 32, 15 mm, OD min. 18 - OD max. 25 mm, Polyamide 6
GTIN (EAN)	4032248536641
Qty.	20 pc(s).

VG K (standard plastic cable gland)
VG M32-K67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	56 mm	Length (inches)	2.205 inch
Net weight	37.5 g		

General information

AF size 1	42 mm	Cable glands	metric
External thread	M 32	Length of thread	15 mm
Material	Polyamide 6	Operating temperature range, max.	100 °C
Operating temperature range, min.	-20 °C	Outer cable diameter, max.	25 mm
Outer cable diameter, min.	18 mm	Pitch of thread	1.5 mm
Protection degree	IP67	Seal insert	NBR
Standards	DIN EN 62444, EN 62444, IEC 62444	Torque for cap nut, max.	13 Nm
Torque for cap nut, min.	12 Nm	Torque for connecting adapter, max.	8.5 Nm
Torque for connecting adapter, min.	7.5 Nm	Torque for lock nut, max.	8.5 Nm
Torque for lock nut, min.	7.5 Nm	UL 94 flammability rating	V-2

Classifications

ETIM 3.0	EC000441	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000441
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-09
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09
eClass 8.1	27-14-91-09	eClass 9.0	27-14-44-32
eClass 9.1	27-14-44-32		

Approvals

Approvals	
ROHS	Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP