

**Conductor markers  
SF 00/21 MC NE GE V2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

**General ordering data**

|            |                                                                         |
|------------|-------------------------------------------------------------------------|
| Type       | SF 00/21 MC NE GE V2                                                    |
| Order No.  | <a href="#">1918560000</a>                                              |
| Version    | Conductor markers, MultiCard, 21 x 3.2 mm, Polyamide 66, Colour: Yellow |
| GTIN (EAN) | 4032248554362                                                           |
| Qty.       | 400 pc(s).                                                              |

## Conductor markers SF 00/21 MC NE GE V2

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |        |            |        |
|--------|--------|------------|--------|
| Length | 21 mm  | Width      | 3.2 mm |
| Height | 3.2 mm | Net weight | 0.21 g |

### General data

|                                              |        |                                   |              |
|----------------------------------------------|--------|-----------------------------------|--------------|
| Colour                                       | Yellow | Material                          | Polyamide 66 |
| Material colour according to resistance code | 4      | Operating temperature range, max. | 100 °C       |
| Operating temperature range, min.            | -40 °C | Size of labelling field           | 21x3.2 mm    |
| Type of printing                             | blank  | UL 94 flammability rating         | V-2          |

### Conductor and cable markers

|                               |                      |                               |                      |
|-------------------------------|----------------------|-------------------------------|----------------------|
| Conductor O.D., max.          | 1.3 mm               | Conductor O.D., min.          | 1 mm                 |
| Conductor cross-section, max. | 0.25 mm <sup>2</sup> | Conductor cross-section, min. | 0.18 mm <sup>2</sup> |
| Halogen                       | No                   |                               |                      |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-03 |
| eClass 7.1 | 27-14-91-03 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Downloads

|                                 |                                     |
|---------------------------------|-------------------------------------|
| M-Print® PRO configuration file | <a href="#">mc_sf_00_21_mcf.zip</a> |
|---------------------------------|-------------------------------------|