

**OMNIMATE Housing - MICROBOX
MHZ 6**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Closed housing, 6.1 mm wide, with six tension clamp connections. The two upper connections can be interconnected with a plug-in cross-connector.

General ordering data

Type	MHZ 6
Order No.	1925760000
Version	Electronics housings, OMNIMATE Housing - MICROBOX , Width: 6.1 mm
GTIN (EAN)	4032248567973
Qty.	10 pc(s).

OMNIMATE Housing - MICROBOX MHZ 6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	92 mm	Width	6.1 mm
Height	97.8 mm	Net weight	31.3 g

System characteristics

Type of connection	Tension clamp connection	Number of connections	6
No. of connection levels	3	Number of PCBs per module	1
PCB thickness	1 mm	Type of contact to PCB	Solder connection, direct
Tolerance for the PCB shape	±0.1 mm	Cross-connection	Yes
Continuous current of cross-connection	10 A	Continuous current of cross-connection/ PCB	32 A
Contact to terminal rail	No	Protection degree	IP 20
Encapsulation option	Yes	Max. power loss	0.8 W

Connectable wires

Clamping range, rated connection, min.	0.13 mm ²	Clamping range, rated connection, max.	2.5 mm ²
Wire connection cross section AWG, min.	AWG 26	Wire connection cross section AWG, max.	AWG 14
Solid, min. H05(07) V-U	0.5 mm ²	Solid, max. H05(07) V-U	2.5 mm ²
Flexible, min. H05(07) V-K	0.5 mm ²	Flexible, max. H05(07) V-K	2.5 mm ²

Material data

UL 94 flammability rating	V-0	Insulating material	Wemid (PA)
Contact material	CuZn	Contact surface	tinned

Rated data according to DIN IEC

Rated current, max. no. of poles (Tu=20°C)	10 A	Rated current, number of poles (Tu=40°C), max.	10 A
Rated voltage for surge voltage class pollution degree II/2	400 V	Rated voltage for surge voltage class pollution degree III/2	320 V
Rated voltage for surge voltage class pollution degree III/3	250 V	Rated impulse voltage for surge voltage class pollution degree II/2	4 kV
Rated impulse voltage for surge voltage class pollution degree III/2	4 kV	Rated impulse voltage for surge voltage class contamination degree III/3	4 kV

Classifications

eClass 6.2	27-26-07-08	eClass 7.1	27-44-04-01
------------	-------------	------------	-------------

Approvals

Approvals	
ROHS	Conform