
OMNIMATE Power - series BV/SV 7.62HP
BVZ 7.62HP/04/180SFC SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com





High-performance female header with the proven, 100% maintenance-free Weidmüller steel clamping yoke. Side-by-side mounting without sacrificing any poles or with patented multifunction flange for secure, fast fixing without tools. Maximum operating reliability thanks to 100% false insertion-proof mating profile, unique coding diversity, incorrect wiring protection, 4-point contact. Suitable for labelling.

- 0.20 - 6 mm² (IEC) / 22 - 10 AWG (UL)
- 800 V (IEC) / 600 V (UL)
- 41 A (IEC) / 35 A (UL)

General ordering data

Type	BVZ 7.62HP/04/180SFC SN BK BX
Order No.	1929760000
Version	PCB plug-in connector, female plug, 7.62 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 6 mm², Box
GTIN (EAN)	4032248579532
Qty.	100 pc(s).
Product data	IEC: 1000 V / 41 A / 0.2 - 6 mm² UL: 600 V / 40.5 A / AWG 24 - AWG 8
Packaging	Box

Erstellungs-Datum January 27, 2014 10:23:12 AM CET

OMNIMATE Power - series BV/SV 7.62HP
BVZ 7.62HP/04/180SFC SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	25.14 g

System parameters

Product family	OMNIMATE Power - series BV/SV 7.62HP	Wire connection method	Clamping yoke connection
Conductor outlet direction	180°	Pitch in mm (P)	7.62 mm
Pitch in inches (P)	0.3 inch	No. of poles	4
Screwdriver blade	0.8 x 4.5	Screwdriver blade standard	DIN 5264
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Clamping screw	M 2.5	Stripping length	12 mm
L1 in mm	22.86 mm	L1 in inches	0.9 inch
Touch-safe protection acc. to DIN VDE 0470	IP 20	Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch

Material data

Insulating material	PA GF	Colour	Black
Colour chart (similar)	RAL 9011	UL 94 flammability rating	V-0
CTI	≥ 500	Contact material	Cu-Leg
Contact surface	tinned	Contact base material	Cu-Leg

Connectable conductors

Clamping range, rated connection, min.	0.2 mm²	Clamping range, rated connection, max.	6 mm²
Wire connection cross section AWG, min.	AWG 22	Wire connection cross section AWG, max.	AWG 10
Solid, min. H05(07) V-U	0.2 mm²	Solid, max. H05(07) V-U	6 mm²
Flexible, min. H05(07) V-K	0.5 mm²	Flexible, max. H05(07) V-K	6 mm²
w. wire end ferrule, DIN 46228 pt 1, min	0.25 mm²	w. wire end ferrule, DIN 46228 pt 1, max.	6 mm²
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.25 mm²	w. plastic collar ferrule, DIN 46228 pt 4, max.	6 mm²
Plug gauge acc. to EN 60999 a x b; Ø	2.8 mm x 2.0 mm; 2.4 mm		

DIN IEC rating data

Rated current, min. no. of poles (TU=20°C)	41 A	Rated current, number of poles (Tu=40°C), min	41 A
Rated voltage for surge voltage class pollution degree II/2	1,000 V	Rated voltage for surge voltage class pollution degree III/2	1,000 V
Rated voltage for surge voltage class pollution degree III/3	800 V	Rated impulse voltage for surge voltage classpollution degree II/2	6 kV
Rated impulse voltage for surge voltage classpollution degree III/2	8 kV	Rated impulse voltage for surge voltage classcontamination degree III/3	8 kV
Short-time withstand current resistance	3 x 1s with 420 A		

OMNIMATE Power - series BV/SV 7.62HP
BVZ 7.62HP/04/180SFC SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

CSA rating data

Institute (CSA)		Rated voltage (Use group B)	600 V
Rated current (use group B)	35 A	Rated voltage (Use group C)	600 V
Rated current (use group C)	35 A	Rated voltage (use group D)	600 V
Rated current (use group D)	5 A	Wire cross-section, AWG, min.	AWG 24
Wire cross-section, AWG, max.	AWG 10		

UL 1059 rating data

Rated voltage (use group B)	600 V	Rated current (use group B)	40.5 A
Rated voltage (use group C)	600 V	Rated current (use group C)	40.5 A
Rated voltage (use group D)	600 V	Rated current (use group D)	5 A
Wire cross-section, AWG, min.	AWG 24	Wire cross-section, AWG, max.	AWG 8

Classifications

UNSPSC	30-21-18-10	eClass 5.1	27-26-07-04
eClass 6.2	27-26-07-04	eClass 7.1	27-44-04-02

Notes

Notes

- Additional colours on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule with plastic collar to DIN 46228/4
- Wire end ferrule without plastic collar to DIN 46228/1
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

Approvals

Approvals


ME25

ROHS	Conform


OMNIMATE Power - series BV/SV 7.62HP
BVZ 7.62HP/04/180SFC SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com


Zeichnungen



BVZ 7.62HP/../180 - SV 7.62HP/../90



BVZ 7.62HP/../180 - SV 7.62HP/../180



BVZ 7.62HP/../180 - SVZ 7.62HP/../180

