

**Bolt-type screw terminals
WF 10 NFF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Product image**Klippon® Connect with stud Technology**

Our stud terminals are an established, robust connection alternative for particularly harsh environments. The extensive accessories and quality workmanship ensure high productivity in planning and installation – and sustainable safety in operation..

General ordering data

Type	WF 10 NFF
Order No.	1968950000
Version	Bolt-type screw terminals, Feed-through terminal, Rated cross-section: 120 mm ² , Threaded stud connection
GTIN (EAN)	4032248702862
Qty.	20 pc(s).

Bolt-type screw terminals WF 10 NFF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	33.8 mm	Width (inches)	1.331 inch
Height	67 mm	Height (inches)	2.638 inch
Depth	72.5 mm	Depth (inches)	2.854 inch
Net weight	101.3 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	Single-stud terminals	Tightening torque (clamping screw for copper conductors)	30...36 Nm
End cover plate required	No	Number of levels	1
No. of clamping points per level	1	Levels cross-connected internally	No
PE connection	No	Rail	TS 35

Additional technical data

Explosion-tested version	No	Number of similar terminals	1
Open sides	Open	Type of mounting	Snap-on

Conductors for clamping (rated connection)

Cable lug to DIN 46234	6...120 mm ²	Cable lug to DIN 46235	10...95 mm ²
Clamping range, max.	120 mm ²	Clamping range, min.	6 mm ²
Number of connections	1	Stud size for spade connection	M 10
Tightening torque, max.	36 Nm	Tightening torque, min.	30 Nm
Type of connection	Threaded stud connection		

Dimensions

TS 35 offset	31.5 mm
--------------	---------

Rating data

Rated cross-section	120 mm ²	Rated voltage	1,000 V
Voltage with epoxy resin partition plate	2,300 V	Rated current	269 A
Current at maximum wires	269 A	Volume resistance according to IEC 60947-7-x	0.12 mΩ
Rated impulse withstand voltage	8 kV	Impulse voltage with epoxy resin partition plate	12 kV
Pollution severity	3		

Bolt-type screw terminals WF 10 NFF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Stud connection

Cable lug to DIN 46234	6...120 mm ²	Cable lug to DIN 46235	10...95 mm ²
Impulse voltage with epoxy resin partition plate	12 kV	Stud size for spade connection	M 10
Tightening torque, max.	36 Nm	Tightening torque, min.	30 Nm
Voltage with epoxy resin partition plate	2,300 V		

Classifications

ETIM 3.0	EC002020	ETIM 4.0	EC000897
ETIM 5.0	EC000897	ETIM 6.0	EC000897
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-20
eClass 6.2	27-14-11-20	eClass 7.1	27-14-11-20
eClass 8.1	27-14-11-20	eClass 9.0	27-14-11-20
eClass 9.1	27-14-11-20		

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	DE_PT1004_20160418_838_ISSUE01.pdf
Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Safety note

Safety notice	Safety Information
---------------	------------------------------------