

HSS-HF 1/8 1.8-2.8/50Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration



The heat-shrinkable TwinMark sleeve is printable on 2 sides and can be used for marking and insulating conductors and cables between 1.2 and 24 mm in diameter. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

Advantages:

- Application in extremely confined spaces
- Printing on 2 sides for better legibility
- Printed sleeves on a continuous backing
- Can be shrunk with conventional hot-air guns

TwinMark HSS-HF, halogen-free variant

Delivered form: reel

General ordering data

Type	HSS-HF 1/8 1.8-2.8/50Y
Order No.	1961900000
Version	Conductor and cable markers, 1.8 - 2.8 mm, 50.8 x 5.7 mm
GTIN (EAN)	4032248642595
Qty.	5,000 pc(s).
compatible printer	2430920000 2448870000 1140490000

HSS-HF 1/8 1.8-2.8/50Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	5.7 mm	Width (inches)	0.224 inch
Height	50.8 mm	Height (inches)	2 inch
Depth	0.77 mm	Depth (inches)	0.03 inch
Net weight	0.524 g		

General data

Halogen	No	Material	Polyolefine
Material colour according to resistance code	4	Operating temperature range	-55...105 °C
Recommended industries	Transportation	Type of printing	neutral
Width	5.7 mm		

Conductor and cable markers

Conductor O.D.	1.8 - 2.8 mm	Conductor O.D., max.	2.8 mm
Conductor O.D., min.	1.8 mm	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.5 mm ²	Halogen	No
Rate of shrinkage	2:1	Recommended shrinking temperature	90 °C

Classifications

ETIM 3.0	EC001530	ETIM 4.0	EC001288
ETIM 5.0	EC001288	ETIM 6.0	EC001530
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-29
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN 45545-2 2013+A1 2015 BS EN ISO 4589-2 1999
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
Software	M-Print PRO configuration file

HSS-HF 1/8 1.8-2.8/50Y

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

