

HSS-HF 3/16 2.8-4.2/25Y

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration



The heat-shrinkable TwinMark sleeve is printable on 2 sides and can be used for marking and insulating conductors and cables between 1.2 and 24 mm in diameter. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

Advantages:

- Application in extremely confined spaces
- Printing on 2 sides for better legibility
- Printed sleeves on a continuous backing
- Can be shrunk with conventional hot-air guns

TwinMark HSS-HF, halogen-free variant

Delivered form: reel

General ordering data

| | |
|--------------------|--|
| Type | HSS-HF 3/16 2.8-4.2/25Y |
| Order No. | 1961980000 |
| Version | Conductor and cable markers, 2.8 - 4.2 mm, 25.4 x 8.4 mm |
| GTIN (EAN) | 4032248642670 |
| Qty. | 8,000 pc(s). |
| compatible printer | 2430920000 2448870000 1140490000 |

HSS-HF 3/16 2.8-4.2/25Y
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data
Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Width | 8.4 mm | Width (inches) | 0.331 inch |
| Height | 25.4 mm | Height (inches) | 1 inch |
| Depth | 0.77 mm | Depth (inches) | 0.03 inch |
| Net weight | 0.355 g | | |

General data

| | | | |
|--|----------------|-----------------------------|--------------|
| Halogen | No | Material | Polyolefine |
| Material colour according to resistance code | 4 | Operating temperature range | -55...105 °C |
| Recommended industries | Transportation | Type of printing | neutral |
| Width | 8.4 mm | | |

Conductor and cable markers

| | | | |
|-------------------------------|---------------------|-----------------------------------|-------------------|
| Conductor O.D. | 2.8 - 4.2 mm | Conductor O.D., max. | 4.2 mm |
| Conductor O.D., min. | 2.8 mm | Conductor cross-section, max. | 4 mm ² |
| Conductor cross-section, min. | 1.5 mm ² | Halogen | No |
| Rate of shrinkage | 2:1 | Recommended shrinking temperature | 90 °C |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC001530 | ETIM 4.0 | EC001288 |
| ETIM 5.0 | EC001288 | ETIM 6.0 | EC001530 |
| UNSPSC | 30-21-18-01 | eClass 5.1 | 27-14-91-29 |
| eClass 6.2 | 27-40-04-01 | eClass 7.1 | 27-14-91-29 |
| eClass 8.1 | 27-14-91-03 | eClass 9.0 | 27-40-04-01 |
| eClass 9.1 | 27-40-04-01 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN 45545-2 2013+A1 2015 BS EN ISO 4589-2 1999 |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| Engineering Data | STEP |
| Software | M-Print PRO configuration file |

Data sheet**HSS-HF 3/16 2.8-4.2/25Y**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings