


RS 80 AP RF 80 LI 2025

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Flexible - More flexible - Profilform

Modular housings in profile form - the flexible modular system comprising coloured and transparent plastic profiles and carrier modules

The combination of standard pitches mounted side by side in any arrangement and metre goods cut accurate to the millimetre creates the perfect balance between flexibility and economic efficiency:

- Pitch profiles with standard widths ranging from 5mm to 45mm allow the mounting of all standard PCB formats.
- Variable heights ensure maximum component density, even with larger electronics components.
- The different installation variations mean that mounting the enclosure directly is as easy as clipping components onto the terminal rail
- Solid hoods protect the module reliably from external influences

The recipe for success: variable profile + modular form components = flexible enclosure concept that offers a large surface area for the PCBs.

The modular concept is designed for modules with high space requirements and suitable for small component quantities and different widths.

General ordering data

Type	AP RF 80 LI 2025
Order No.	8156210000
Version	End plate, RS 80 Pebble grey, End plate, Width: 9 mm
GTIN (EAN)	4008190978198
Qty.	20 pc(s).

RS 80
AP RF 80 LI 2025

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	86.4 mm	Length (inches)	3.402 inch
Width	9 mm	Width (inches)	0.354 inch
Height	30 mm	Height (inches)	1.181 inch
Net weight	6 g		

System characteristics

Version	End plate	Cross-connection	No
Contact to terminal rail	No	Protection degree	IP20
Encapsulation option	No		

Material data

Insulating material	PA 66	Colour	Pebble grey
Colour chart (similar)	RAL 7032	CTI	≥ 600
UL 94 flammability rating	V-2	Storage temperature, min.	-25 °C
Storage temperature, max.	85 °C	Max. relative humidity during storage	80 %
Operating temperature, min.	-50 °C	Operating temperature, max.	100 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	100 °C

Classifications

ETIM 3.0	EC000886	ETIM 5.0	EC000886
ETIM 6.0	EC001031	UNSPSC	30-21-18-27
eClass 5.1	27-14-11-33	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33	eClass 8.1	27-14-11-33
eClass 9.0	27-18-27-90	eClass 9.1	27-18-27-90

Notes

Notes

Descriptive text technical data

3 heights are available for the cover profile and the end plates:**TS mounting without cover: TS 32 = 45 mm, TS35x7.5 = 40.5 mm****TS mounting with low cover: TS 32 = 72 mm, TS 35x7.5 = 67.5 mm****TS mounting with high cover: TS 32 = 91 mm, TS 35x7.5 = 86.5 mm****Direct mounting, without/low/high cover: 17 / 44 / 63 mm****Dimensions of the PCB:****Thickness: 1.6 (±0.2) mm, width: 67.8 (+0.2) mm****Dimension of the RS section = length of the printed circuit board - 4.5 mm****Dimension ADP section = PCB length - 2 mm****Example:****PCB length 160 mm, RS section = 155.5 mm, ADP section = 158 mm****Approvals**

Approvals



ROHS

Conform

Creation date May 28, 2019 2:34:39 PM CEST

Catalogue status 23.05.2019 / We reserve the right to make technical changes.

2

Data sheet**RS 80**
AP RF 80 LI 2025**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Technical data****Downloads**

Brochure/Catalogue	FL ANALO.SIGN.CONV. EN MB DEVICE MANUF. EN CAT 2 PORTFOLIOGUIDE EN FL MACHINE SAFETY EN FL 72H SAMPLE SER EN PO OMNIMATE EN
Engineering Data	EPLAN
