

DK-SERIES
DK OR 35 24VDC
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Logic functions AND, NAND, OR and NOR in modular terminal format with a rated cross-section of 4 mm². They each have five inputs which are fed – with logic gating – via a 24 V/20 mA PNP output. The logic components can be used for many applications involving the coupling of digital sensor/actuator signals with automation devices.

General ordering data

Type	DK OR 35 24VDC
Order No.	8218440000
Version	Function component, OR Gate
GTIN (EAN)	4008190191252
Qty.	5 pc(s).

DK-SERIES
DK OR 35 24VDC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	65 mm	Length (inches)	2.559 inch
Width	12 mm	Width (inches)	0.472 inch
Height	57 mm	Height (inches)	2.244 inch
Net weight	29.2 g		

Temperatures

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature, max.	50 °C
Operating temperature, min.	0 °C	Storage temperature, max.	60 °C
Storage temperature, min.	-40 °C	Operating temperature	0 °C...50 °C
Storage temperature	-40 °C...60 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Input

Number of inputs	5	Pulse duration	≥ 50 µs
Rated input level	24 V DC= High, 0 V = Low	Rated voltage (text)	Max. 30 V
Input current	Approx. 1.5 mA per input (24 V)		

Output

Number of outputs	1	Output current	max. 20 mA
Output level	PNP, Ub-1.8 V	Switching thresholds	High <15 V, low < 9 V
load impedance current	≤ 600 Ω		

General data

Current consumption	< 5 mA	Galvanic isolation	Without isolation
Humidity	40 °C / 93 % rel. humidity, no condensation	Input/Output	Logic module
Open sides	right	Rail	TS 35
Type of connection	Screw connection	Voltage supply	24...30 V DC

Insulation coordination

Insulation voltage input or output/rail	4 kV _{eff}	Standards	DIN EN 50178
---	---------------------	-----------	--------------

Connection data

Type of connection	Screw connection	Clamping range, rated connection	4 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	4 mm ²

Classifications

ETIM 4.0	EC001417	ETIM 5.0	EC001417
ETIM 6.0	EC001417	UNSPSC	30-21-18-01
eClass 5.1	27-24-22-16	eClass 6.2	27-24-22-16
eClass 7.1	27-24-22-16	eClass 8.1	27-24-22-16
eClass 9.0	27-24-22-16	eClass 9.1	27-21-92-90

DK-SERIES DK OR 35 24VDC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of
Conformity

[Declaration of Conformity.pdf](#)

Engineering Data

[EPLAN, WSCAD](#)

DK-SERIES DK OR 35 24VDC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

