

**RIDERSERIES  
RCH S21024**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Product image**


Similar to illustration

- Relay with positively driven contacts acc. to EN 50205
- 2 CO contacts or 1 NOC + 1 NCC
- 1500 VA switching capacity
- 6 kV impulse withstand voltage

**General ordering data**

Type	RCH S21024
Order No.	<a href="#">8768680000</a>
Version	RIDERSERIES, Relay, No. of contacts: 2 CO contact AgNi, Rated control voltage: 24 V DC, Continuous current: 6 A, Screw connection
GTIN (EAN)	4032248437474
Qty.	20 pc(s).

**RIDERSERIES  
RCH S21024**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Length	29 mm	Length (inches)	1.142 inch
Width	12.6 mm	Width (inches)	0.496 inch
Height	25.5 mm	Height (inches)	1.004 inch
Net weight	19.65 g		

**Temperatures**

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-25 °C	Operating temperature	-25 °C...70 °C
Storage temperature			

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Rated data UL**

Certificate No. (cURus)	E223474
-------------------------	---------

**Input**

Rated control voltage	24 V DC	Rated current DC	29.2 mA
Power rating	700 mW	Pull-in/drop-out voltage, typ.	18 V / 2.4 V DC
Status indicator	No		

**Output**

Rated switching voltage	250 V AC	Max. switching voltage, AC	250 V
Continuous current	6 A	Switch-on delay	≤ 10 ms
Switch-off delay	≤ 4 ms		

**Contact data**

Contact type	2 CO contact (AgNi)	Mechanical service life	10 x 10 <sup>6</sup> switching cycles
--------------	---------------------	-------------------------	---------------------------------------

**General data**

Test button	No	Mechanical switch position indicator	No
Colour	Transparent		

**Insulation coordination**

Surge voltage category	III	Pollution severity	2
Protection degree	IP20	Creepage and clearance distance input – output	≥ 8 mm
Creepage and clearance distances between contacts	5.5 mm		

**Further details of approvals / standards**

Standards	IEC 61810-1, UL508	Certificate No. (cURus)	E223474
-----------	--------------------	-------------------------	---------

**Data sheet**

**RIDERSERIES  
RCH S21024**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Connection data**

Wire connection method	Screw connection	Pitch in mm (P)	5 mm
------------------------	------------------	-----------------	------

**Classifications**

ETIM 3.0	EC001437	ETIM 4.0	EC001437
ETIM 5.0	EC001437	ETIM 6.0	EC001437
UNSPSC	30-21-19-17	eClass 5.1	27-37-16-01
eClass 6.2	27-37-16-01	eClass 7.1	27-37-16-01
eClass 8.1	27-37-16-01	eClass 9.0	27-37-16-01
eClass 9.1	27-37-16-01		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Engineering Data [EPLAN, WSCAD](#)


**RIDERSERIES  
RCH S21024**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings****Wiring diagram**

**Circuit diagram**  
View of connections

2 changeover contacts



1 NOC + 1 NCC

