

**RIDERSERIES
RCH S51024**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Product image


Similar to illustration

- Relay with positively driven contacts acc. to EN 50205
- 2 CO contacts or 1 NOC + 1 NCC
- 1500 VA switching capacity
- 6 kV impulse withstand voltage

General ordering data

Type	RCH S51024
Order No.	8768700000
Version	RIDERSERIES, Relay, No. of contacts: 1 NC and NO contact AgNi, Rated control voltage: 24 V DC, Continuous current: 6 A, Screw connection
GTIN (EAN)	4032248437481
Qty.	20 pc(s).

Data sheet

RIDERSERIES RCH S51024

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	29 mm	Length (inches)	1.142 inch
Width	12.6 mm	Width (inches)	0.496 inch
Height	25.5 mm	Height (inches)	1.004 inch
Net weight	19.2 g		

Temperatures

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-25 °C	Operating temperature	-25 °C...70 °C
Storage temperature			

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Rated data UL

Certificate No. (cURus)	E223474
-------------------------	---------

Input

Rated control voltage	24 V DC	Rated current DC	29.2 mA
Power rating	700 mW	Pull-in/drop-out voltage, typ.	18 V / 2.4 V DC
Status indicator	No		

Output

Rated switching voltage	250 V AC	Max. switching voltage, AC	250 V
Continuous current	6 A	Switch-on delay	≤ 10 ms
Switch-off delay	≤ 4 ms		

Contact data

Contact type	1 NC and NO contact (AgNi)	Mechanical service life	10 x 10 ⁶ switching cycles
--------------	-------------------------------	-------------------------	---------------------------------------

General data

Test button	No	Mechanical switch position indicator	No
Colour	Transparent		

Insulation coordination

Surge voltage category	III	Pollution severity	2
Protection degree	IP20	Creepage and clearance distance input – output	≥ 8 mm
Creepage and clearance distances between contacts	5.5 mm		

Further details of approvals / standards

Standards	IEC 61810-1, UL508	Certificate No. (cURus)	E223474
-----------	--------------------	-------------------------	---------

Creation date May 28, 2019 2:44:22 PM CEST

Data sheet

**RIDERSERIES
RCH S51024**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Connection data

Wire connection method	Screw connection	Pitch in mm (P)	5 mm
------------------------	------------------	-----------------	------

Classifications

ETIM 3.0	EC001437	ETIM 4.0	EC001437
ETIM 5.0	EC001437	ETIM 6.0	EC001437
UNSPSC	30-21-19-17	eClass 5.1	27-37-16-01
eClass 6.2	27-37-16-01	eClass 7.1	27-37-16-01
eClass 8.1	27-37-16-01	eClass 9.0	27-37-16-01
eClass 9.1	27-37-16-01		

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [EPLAN, WSCAD](#)


**RIDERSERIES
RCH S51024**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings**Wiring diagram**

Circuit diagram
View of connections

2 changeover contacts



1 NOC + 1 NCC

