

## Connecting elements

### H0,75/14 W BD GSP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

#### General ordering data

|            |   |
|------------|---|
| Type       | H0,75/14 W BD GSP                               |
| Order No.  | <a href="#">9005820000</a>                      |
| Version    | Wire-end ferrule, insulated, 10 mm, 8 mm, white |
| GTIN (EAN) | 4008190275884                                   |
| Qty.       | 5,000 pc(s).                                    |
| Packaging  | Reel  |

**Data sheet**

**Connecting elements  
H0,75/14 W BD GSP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

|            |        |                |            |
|------------|--------|----------------|------------|
| Width      | 14 mm  | Width (inches) | 0.551 inch |
| Net weight | 0.12 g |                |            |

**Technical data**

|         |           |
|---------|-----------|
| Version | insulated |
|---------|-----------|

**Wire-end ferrules**

|                             |                      |   |            |
|-----------------------------|----------------------|---|------------|
| Collar diameter (D2)        | 2.8 mm               | Colour code                             | Weidmüller |
| Conductor cross-section     | 0.75 mm <sup>2</sup> | Contact surface diameter (D1)           | 1.2 mm     |
| Contact surface length (L2) | 8 mm                 | L1 in mm                                | 14 mm      |
| Metal sleeve thickness (S1) | 0.15 mm              | Plastic collar thickness (S2)           | 0.25 mm    |
| Stripping length            | 10 mm                | Wire connection cross section AWG, max. | AWG 18     |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000005    | ETIM 4.0   | EC000005    |
| ETIM 5.0   | EC000005    | ETIM 6.0   | EC000005    |
| UNSPSC     | 31-16-31-02 | eClass 5.1 | 27-40-02-01 |
| eClass 6.2 | 27-40-02-01 | eClass 7.1 | 27-40-02-01 |
| eClass 8.1 | 27-40-02-01 | eClass 9.0 | 27-40-02-01 |
| eClass 9.1 | 27-40-02-01 |            |             |

**Approvals**

Approvals



ROHS Conform

**Downloads**

|                    |  |
|--------------------|--|
| Brochure/Catalogue | <a href="#">CAT 6 TOOLS 15/16 EN</a>     |
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a> |
| Engineering Data   | <a href="#">STEP</a>                     |

**Data sheet**

**Connecting elements  
H0,75/14 W BD GSP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Similar to illustration**

---

