

MCZ SERIES
MCZ OVP CL 48VUC 0,5A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Slimline overvoltage protection terminal with tension clamp connection

- 6 mm Slimline fine overvoltage protection
- fast wiring thanks to TS contact and tension clamp connections
- can be cross-connected

General ordering data

Type	MCZ OVP CL 48VUC 0,5A
Order No.	8449000000
Version	MCZ SERIES, Surge protection for instrumentation and control, 0.5 A
GTIN (EAN)	4008190156114
Qty.	10 pc(s).

MCZ SERIES

MCZ OVP CL 48VUC 0,5A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Width	6 mm	Width (inches)	0.236 inch
Height	91 mm	Height (inches)	3.583 inch
Depth	63.5 mm	Depth (inches)	2.5 inch
Net weight	25.4 g		

Temperatures

Operating temperature, max.	60 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	85 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...60 °C	Storage temperature	-40 °C...85 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Rated data UL

Certificate No. (UL)	E311081
----------------------	---------

General data

Colour	black	Design	Terminal
Height with TS 35	63.5 mm	Protection degree	IP20
Rail	TS 35	Segment	Measurement - Monitoring - Setting
UL 94 flammability rating	V-0	Version	Surge protection for measurement and control

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Rated data IEC / EN

Discharge current, I_{imp} (10/350 μ s)	2.5 kA	Discharge current, max. (8/20 μ s)	5 kA
Fuse	0.5 A	Inductance L and L1	75 μ H
Lightning test current I_{imp} (10/350 μ s)	2.5 kA	Limiting frequency (-3 dB) at load resistance	500 kHz 240 Ω
Load resistance (for limiting frequency)	240 Ω	Max. continuous voltage, U_c (AC)	53 V
Operating current, I_{max}	0.5 A	Operating voltage	75 V
Protection level on output side Wire-PE 1kV/ μ s, typically	80 V	Protection level on output side Wire-PE 8/20 μ s, typically	150 V
Protection level on output side Wire-wire 1 kV/ μ s, typically	82 V	Protection level on output side Wire-wire 8/20 μ s, typically	150 V
Rated current I_N	0.5 A	Rated voltage (AC)	48 V
Rated voltage (DC)	48 V	Rated voltage (DC), max.	70 V
Requirements category acc. to IEC 61643-21	D1	Response time	≤ 100 ps
Standards	HART-compatible	Voltage type	AC/DC
Volume resistance	2.50 Ω		

MCZ SERIES
MCZ OVP CL 48VUC 0,5A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Connection data**

Cross-section	1.5 mm ²	Wire connection method	Tension-clamp connection
Type of connection	Tension-clamp connection	Stripping length, rated connection	8 mm
Clamping range, rated connection	1.5 mm ²	Clamping range, min.	0.5 mm ²
Clamping range, max.	1.5 mm ²	Wire connection cross section AWG, min.	AWG 26
Wire connection cross section AWG, max.	AWG 16	Wire cross-section, solid, min.	0.5 mm ²
Wire cross-section, solid, max.	1.5 mm ²	Wire connection cross-section, finely stranded, min.	0.5 mm ²
Wire connection cross section, finely stranded, max.	1.5 mm ²	Wire cross-section, finely stranded, min. (AWG)	AWG 26
Wire cross-section, finely stranded, max. (AWG)	AWG 16	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	1.5 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), min.	0.5 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), max.	1.5 mm ²	Blade size	0.6 x 3.5 mm

Classifications

ETIM 3.0	EC000943	ETIM 4.0	EC000381
ETIM 5.0	EC000381	ETIM 6.0	EC000943
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-27
eClass 6.2	27-13-08-02	eClass 7.1	27-13-08-02
eClass 8.1	27-13-08-02	eClass 9.0	27-13-08-07
eClass 9.1	27-13-08-07		

Approvals

Approvals



ROHS

Conform

Downloads


Approval/Certificate/Document of Conformity	CE PAPER Declaration of Conformity
Brochure/Catalogue	CAT 4.4 ELECTR 16/17 EN
Engineering Data	EPLAN.WSCAD
Engineering Data	STEP
User Documentation	Instruction sheet

MCZ SERIES MCZ OVP CL 48VUC 0,5A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Electric symbol



Circuit diagram