


OMNIMATE Housing - TERMINALBOX MCZ 5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Open miniature housing in modular terminal format with five tension clamp connections. A transparent hinged top plate can be used for labelling and provides access to potentiometer and status displays. Plug-in cross-connectors can be used to interconnect the three top connections. A cover plate for closing off the housing is also available.

General ordering data

Type	MCZ 5
Order No.	8857560000
Version	Electronics housings, OMNIMATE Housing - TERMINALBOX grey-beige, Terminal support, Width: 6 mm
GTIN (EAN)	4032248575718
Qty.	10 pc(s).

**OMNIMATE Housing - TERMINALBOX
MCZ 5**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	91 mm	Length (inches)	3.583 inch
Width	6 mm	Width (inches)	0.236 inch
Height	63 mm	Height (inches)	2.48 inch
Net weight	4.74 g		

System characteristics

Version	Terminal support	Type of connection	Tension-clamp connection
Number of connections	5	Number of connection levels	2
Number of PCBs per module	1	PCB thickness	1 mm
Type of contact to PCB	Solder connection, direct	Tolerance for the PCB shape	±0.1 mm
Cross-connection	Yes	Continuous current of cross-connection	10 A
Continuous current of cross-connection/ PCB	32 A	Contact to terminal rail	No
Protection degree	IP20	Encapsulation option	Yes
Max. power loss	0.8 W		

Material data

Colour	grey-beige	Insulating material group	IIIa
CTI	≥ 600	UL 94 flammability rating	V-0
Contact base material	CuZn	Contact material	CuZn
Contact surface	tinned	Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C	Max. relative humidity during storage	80 %
Operating temperature, min.	-50 °C	Operating temperature, max.	120 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	120 °C

Rated data acc. to IEC

Rated current, max. no. of poles (Tu=20°C)	10 A	Rated current, max. no. of poles (Tu=40°C)	10 A
Rated voltage for surge voltage class / pollution degree II/2	400 V	Rated voltage for surge voltage class / pollution degree III/2	320 V
Rated voltage for surge voltage class / pollution degree III/3	250 V	Rated impulse voltage for surge voltage class/ pollution degree II/2	4 kV
Rated impulse voltage for surge voltage class/ pollution degree III/2	4 kV	Rated impulse voltage for surge voltage class/ contamination degree III/3	4 kV

Classifications

ETIM 6.0	EC000261	UNSPSC	30-21-18-01
eClass 6.2	27-18-09-90	eClass 7.1	27-18-09-90
eClass 8.1	27-18-09-90	eClass 9.0	27-18-01-90
eClass 9.1	27-18-92-90		

Notes

Notes

Data sheet**OMNIMATE Housing - TERMINALBOX
MCZ 5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS

Conform

Downloads

Brochure/Catalogue

[FL ANALO.SIGN.CONV. EN](#)
[MB DEVICE MANUF. EN](#)
[CAT 2 PORTFOLIOGUIDE EN](#)
[FL MACHINE SAFETY EN](#)
[FL 72H SAMPLE SER EN](#)
[PO OMNIMATE EN](#)

Engineering Data

[PCB contour with soldering pads](#)