

**RIDERSERIES RRD
SRD-I CLIP M**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

The ideal relay version for the separation of input and output signals in industrial automation.

High powers can be safely switched with the RIDERSERIES.

Conventional relays and LED indicators are simply plugged in, retaining and disassembly clips provide a secure fixing.

General ordering data

Type	SRD-I CLIP M
Order No.	8869370000
Version	RIDERSERIES RRD, Retaining clip
GTIN (EAN)	40322486 14707
Qty.	25 pc(s).

Data sheet

**RIDERSERIES RRD
SRD-I CLIP M**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 0.9 g

Temperatures

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...85 °C		

General data

Material metal Colour silver

Insulation coordination

Protection degree IP20

Classifications

ETIM 4.0	EC001456	ETIM 5.0	EC002586
ETIM 6.0	EC002586	UNSPSC	30-21-19-17
eClass 5.1	27-37-16-03	eClass 6.2	27-37-16-03
eClass 7.1	27-37-92-08	eClass 8.1	27-37-92-08
eClass 9.1	27-37-16-92		

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [EPLAN, WSCAD](#)