





| | |
|-------------------------------------|--|
| Nominal Voltage: | 1.5 V |
| Operating Voltage | 1.6 - 0.75V |
| Impedance: | 136 m-ohm @ 1kHz |
| Typical Weight: | 139 gm (4.9 oz.) |
| Typical Volume: | 56.4 cm ³ (3.4 in. ³) |
| Terminals: | Flat |
| Storage Temperature Range: | -20 ^o C to 35 ^o C |
| Operating Temperature Range: | -20 ^o C to 54 ^o C (-4 ^o F to 130 ^o F) |
| ANSI: | 13A |
| IEC: | LR20 |



TYPICAL DISCHARGE CHARACTERISTICS AT 21^oC (70^oF)




DURACELL[®] BATTERIES


Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
Internet: www.duracell.com

* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.


TYPICAL CONSTANT POWER DISCHARGE CHARACTERISTICS AT 21°C (70°F)




TYPICAL CONSTANT CURRENT DISCHARGE CHARACTERISTICS AT 21°C (70°F)




TYPICAL DISCHARGE CHARACTERISTICS AT 21°C (70°F)



TYPICAL DISCHARGE CHARACTERISTICS AT 21°C (70°F)



TYPICAL FLASHLIGHT TEST AT 21°C AND 0°C



DURACELL[®]

BATTERIES

Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
Internet: www.duracell.com

* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.