



Ultra CR2

Lithium/Manganese Dioxide




Nominal Voltage:	3.0 V
rtonina voltago.	3.0 V
Typical Voltage:	3.2-3.3 V
Nominal Internal Impedance:	0.3 ohm @ 1kHz
Average Weight:	11 g
Volume:	5.168 cm. ³
Terminals:	Flat, Recessed Negative Terminal, Nickel Plated Steel
Operating Temp. Range:	-20°C to 75°C (-4°F to 167°F)
NEDA/ANSI:	CR2
IEC:	-

Delivered Energy vs. Power Drain @ Various Cutoff Voltage - Room Temperature




Duracell Ultra CR2 Typical Performance





^{*} Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.




Ultra CR2 **Lithium/Manganese Dioxide**









DURACELI **BATTERIES**

Berkshire Corporate Park Bethel, CT 06801 U.S.A.

Telephone: Toll-free 1-800-544-5454

Internet: www.duracell.com

^{*} Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.