



SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Name of product Anti-Seize ASW High-Tech Assembly Paste
Code-Nr. 261000

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended intended purpose(s)

Corrosion Protection and Lubricant

1.3. Details of the supplier of the safety data sheet

Distributor

WEICON GmbH & Co. KG
Königsberger Str. 255, DE-48157 Münster
Postbox 48045, DE-8460 Münster
Phone ++49(0)251 / 9322 - 0, Fax ++49(0)251 / 9322 - 244
E-Mail : msds@weicon.de
Internet : www.weicon.de

Advice

Produktsicherheit / Product-Safety-Department
Phone ++49(0)251 / 9322 - 0
E-mail (competent person):
msds@weicon.de

1.4. Emergency telephone number

GIZ Bonn (German, English) Tel: ++49(0)228-19 240
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178
433 7434 (24h Emergency Contact)

Manufacturer

WEICON GmbH & Co. KG
Königsberger Str. 255, DE-48157 Münster

1.4. Emergency telephone number

Emergency advice

-
Phone -
GIZ Bonn (Medizinische Auskunft in Deutsch und Englisch)
Tel: ++49(0)228-19 240
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178
433 7434 (24h Emergency Contact)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]

Hazard classes and Hazard categories	Hazard Statements	Classification procedure
--------------------------------------	-------------------	--------------------------

Skin Irrit. 2	H315	
---------------	------	--

Eye Dam. 1	H318	
------------	------	--

Hazard Statements

H315 Causes skin irritation.

H318 Causes serious eye damage.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008 [CLP/GHS]



GHS05

Signal word

Danger

Hazard Statements

H315 Causes skin irritation.
 H318 Causes serious eye damage.

Precautionary Statements

P102 Keep out of reach of children.
 P264 Wash hands thoroughly after handling.
 P280 Wear protective gloves/protective clothing/eye protection/face protection.
 P302 + P352 IF ON SKIN: Wash with plenty of soap and water.
 P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P310 Immediately call a POISON CENTER or doctor/physician.
 P332 + P313 If skin irritation occurs: Get medical advice/attention.
 P362 Take off contaminated clothing.
 P501 Dispose of contents/container to hazardous or special waste collection point.

Hazardous ingredients for labeling

calcium hydroxide

2.3. Other hazards

Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

SECTION 3: Composition/ information on ingredients

3.1. Substances

not applicable

3.2. Mixtures

Description

Mixture of inorganic thickener in mineral oil with additives.

Hazardous ingredients

CAS No	EC No	Name	[% weight]	Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]
1305-62-0	215-137-3	calcium hydroxide	10 - 25	Eye Dam. 1, H318 / Skin Irrit. 2, H315 / STOT SE 3, H335



SECTION 4: First aid measures

4.1. Description of first aid measures

General information

Remove moisted clothing immediately.

In case of inhalation

Remove the casualty into fresh air and keep him immobile.
In the event of symptoms refer for medical treatment.

In case of skin contact

In case of contact with skin wash off with soap and water.
Consult a doctor if skin irritation persists.

In case of eye contact

In case of contact with eyes rinsing with plenty of lukewarm water carefully and seek for medical treatment.

In case of ingestion

Refer to medical treatment.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Alcohol-resistant foam
Dry fire-extinguishing substance
Carbon dioxide
Water spray jet

Unsuitable extinguishing media

Full water jet

5.2. Special hazards arising from the substance or mixture

In case of fire formation of dangerous gases possible.
Carbon monoxide (CO)
Carbon dioxide (CO₂)
Sulphur dioxide (SO₂)

5.3. Advice for firefighters

Special protective equipment for fire-fighters

Fire-fighting operations, rescue and clearing work under effect of combustion and smoulder gases just may be done with breathing apparatus.
Do not inhale explosion and/or combustion gases.

Additional information

Collect contaminated firefighting water separately, must not be discharged into the drains.



SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

High risk of slipping due to leakage/spillage of product.

6.2. Environmental precautions

Do not discharge into the drains/surface waters/groundwater.

6.3. Methods and material for containment and cleaning up

Take up mechanically and send for disposal.

6.4. Reference to other sections

Safe handling: see section 7

Disposal: see section 13

Personal protection equipment: see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

No special measures necessary if used correctly.

General protective measures

Avoid contact with eyes and skin

Hygiene measures

At work do not eat, drink and smoke.

Wash hands before breaks and after work.

Advice on protection against fire and explosion

No special measures necessary.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep in closed original container.

Advice on storage compatibility

Do not store together with acids.

Do not store together with oxidizing agents.

Further information on storage conditions

Recommended storage temperature: room temperature.

7.3. Specific end use(s)

Recommendation(s) for intended use

See section 1.2

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Ingredients with occupational exposure limits to be monitored

CAS No	Name	Code	[mg/m3]	[ppm]	Remark
1305-62-0	Calcium hydroxide	8 hours	5		EH40/2005
13463-67-7	Titanium dioxide: total inhalable dust	8 hours	10		EH40/2005

**Ingredients with occupational exposure limits to be monitored (continued)**

CAS No	Name	Code	[mg/m ³]	[ppm]	Remark
13463-67-7	Titanium dioxide: respirable dust	8 hours	4		EH40/2005

Additional advice

The statutory local and national regulations have to be observed.

8.2. Exposure controls**Respiratory protection**

Not required

Hand protection

In the cases of special applications, it is recommended to check the chemical resistance with the manufacturer of the gloves.

Not suitable: leather gloves

Not suitable: gloves made of thick material

Glove material specification [make/type, thickness, permeation time/life, wetting resistance]: Nitrile rubber; 0,4mm; 480min;60min.

Chemical protective gloves must be chosen carefully in view of their design and depending on the dependence on the concentration and amounts of dangerous goods used in the specific working tasks.

Eye protection

tightly fitting goggles

Other protection measures

protective clothing

Appropriate engineering controls

Sufficient ventilation and exhaustion.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties****Appearance**

pasty

Colour

white

Odour

hardly noticeable

Odour threshold

not determined

Important health, safety and environmental information

	Value	Temperature	at	Method	Remark
pH value	not determined				
boiling point	not determined				
melting point	not determined				
Flash point	> 200 °C			ISO 2592	basic oil
Vapourisation rate	not determined				
Flammable (solid)	not determined				
Flammability (gas)	not determined				
Ignition temperature	not determined				



Safety Data Sheet according to Regulation (EC)

No. 1907/2006 (REACH)

Printed 06.01.2016

revision 12.08.2015 (GB) Version 8.4

Anti-Seize ASW High-Tech Assembly Paste

	Value	Temperature	at	Method	Remark
Self ignition temperature	not determined				
Lower explosion limit	not determined				
Upper explosion limit	not determined				
Vapour pressure	not determined				
Relative density	1,4 g/cm ³	20 °C		DIN 51757	
Vapour density	not determined				
Solubility in water					insoluble
Solubility/other	not determined				
Partition coefficient n-octanol/water (log P O/W)	not determined				
Decomposition temperature	not determined				
Viscosity kinematic	not applicable				

Oxidising properties

No information available.

Explosive properties

not determined

9.2. Other information

No information available.

SECTION 10: Stability and reactivity

10.1. Reactivity

No information available.

10.2. Chemical stability

No information available.

10.3. Possibility of hazardous reactions

Reactions with strong acids.

Reactions with strong oxidising agents.

10.4. Conditions to avoid

No information available.

10.5. Incompatible materials

Substances to avoid

Reactions with strong acids.

Reactions with strong oxidising agents.

10.6. Hazardous decomposition products

Hydrogen sulphides



Thermal decomposition

Remark No decomposition if used as directed.

! SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity/Irritation/Sensitization

	Value/Validation	Species	Method	Remark
Skin irritation	irritant			
Eye irritation	irritant - risk of strong eye injuries			
Skin sensitization	non-sensitizing			

Experiences made from practice

Risk of strong eye injuries.
Irritates mucous membranes.
Irritates eyes and skin.

Additional information

The product is to be handled with the caution usual with chemicals.
Other hazardous properties may not be excluded.

SECTION 12: Ecological information

12.1. Toxicity

No information available.

12.2. Persistence and degradability

No information available.

12.3. Bioaccumulative potential

No information available.

12.4. Mobility in soil

No information available.

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

12.6. Other adverse effects

General regulation

Do not allow uncontrolled leakage of product into the environment.
Product is not allowed to be discharged into the ground water or aquatic environment.
Product is not allowed to be discharged into aquatic environment, drains or sewage treatment plants.



SECTION 13: Disposal considerations

13.1. Waste treatment methods

Recommendations for the product

Remove in accordance with local official regulations.

Recommendations for packaging

Dispose of according to the local waste regulations.

General information

Assignment to a waste code number / waste identification according to the EWC is to be carried out on a sector or process-specific basis.

SECTION 14: Transport information

	ADR/RID	IMDG	IATA-DGR
14.1. UN number	-	-	-
14.2. UN proper shipping name	-	-	-
14.3. Transport hazard class(es)	-	-	-
14.4. Packing group	-	-	-
14.5. Environmental hazards	-	-	-
14.6. Special precautions for user	No information available.		
14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	not applicable		
Transport/further information	No dangerous goods as defined by the transport regulations - ADR/RID, IMDG, ICAO/IATA-DGR.		

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC standard

VOC content 0 %

15.2. Chemical Safety Assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information

Recommended uses and restrictions

National and local regulations concerning chemicals shall be observed.

For industrial use only.

Further information

Each user is responsible for the implementation of the national special regulations.

The information contained herein is based on the state of our knowledge. It characterizes the product with regard to the appropriate safety precautions. It does not represent a guarantee of the properties of the product.



Safety Data Sheet according to Regulation (EC)

No. 1907/2006 (REACH)

Printed 06.01.2016

revision 12.08.2015 (GB) Version 8.4

Anti-Seize ASW High-Tech Assembly Paste

Please observe the following disclaimer! --- Our safety data sheets have been compiled according to effective EU-directives, WITHOUT taking into account the special national directives concerning the handling of hazardous substances.

Indication of changes: "!" = Data changed compared with the previous version. Previous version: 8.3

H315 Causes skin irritation.
H318 Causes serious eye damage.
H335 May cause respiratory irritation.