

Connecting elements

H6,0,0/20T GN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| | |
|------------|--|
| Type | H6,0,0/20T GN |
| Order No. | 9021130000 |
| Version | Wire-end ferrule, insulated, 14 mm, 12 mm, green |
| GTIN (EAN) | 4008190111731 |
| Qty. | 100 pc(s). |
| Packaging | loose |

Connecting elements
H6,0,0/20T GN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|--------|----------------|------------|
| Width | 20 mm | Width (inches) | 0.787 inch |
| Net weight | 0.36 g | | |

Technical data

| | |
|---------|-----------|
| Version | insulated |
|---------|-----------|

Wire-end ferrules

| | | | |
|---|-------------------|-------------------------------|---------------|
| Collar diameter (D2) | 6.3 mm | Colour code | Telemecanique |
| Conductor cross-section | 6 mm ² | Contact surface diameter (D1) | 3.5 mm |
| Contact surface length (L2) | 12 mm | L1 in mm | 20 mm |
| Metal sleeve thickness (S1) | 0.2 mm | Military designation | T 20A 023 A |
| Plastic collar thickness (S2) | 0.3 mm | Stripping length | 14 mm |
| Wire connection cross section AWG, max. | AWG 10 | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000005 | ETIM 4.0 | EC000005 |
| ETIM 5.0 | EC000005 | ETIM 6.0 | EC000005 |
| UNSPSC | 31-16-31-02 | eClass 5.1 | 27-40-02-01 |
| eClass 6.2 | 27-40-02-01 | eClass 7.1 | 27-40-02-01 |
| eClass 8.1 | 27-40-02-01 | eClass 9.0 | 27-40-02-01 |
| eClass 9.1 | 27-40-02-01 | | |

Approvals

Approvals



ROHS Conform

Downloads

| | |
|--------------------|--|
| Brochure/Catalogue | CAT 6 TOOLS 15/16 EN |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| Engineering Data | STEP |