

**Connecting elements**  
**H0,75/14DS GR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

**General ordering data**

|            |                                                |
|------------|------------------------------------------------|
| Type       | H0,75/14DS GR                                  |
| Order No.  | <a href="#">9028580000</a>                     |
| Version    | Wire-end ferrule, insulated, 10 mm, 8 mm, grey |
| GTIN (EAN) | 4032248159475                                  |
| Qty.       | 500 pc(s).                                     |
| Packaging  | loose                                          |

## Connecting elements

### H0,75/14DS GR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|            |         |                |            |
|------------|---------|----------------|------------|
| Width      | 14 mm   | Width (inches) | 0.551 inch |
| Net weight | 0.094 g |                |            |

### Technical data

|         |           |
|---------|-----------|
| Version | insulated |
|---------|-----------|

### Wire-end ferrules

|                             |                      |                                         |         |
|-----------------------------|----------------------|-----------------------------------------|---------|
| Collar diameter (D2)        | 3.4 mm               | Colour code                             | DIN     |
| Conductor cross-section     | 0.75 mm <sup>2</sup> | Contact surface diameter (D1)           | 1.2 mm  |
| Contact surface length (L2) | 8 mm                 | L1 in mm                                | 14 mm   |
| Metal sleeve thickness (S1) | 0.15 mm              | Plastic collar thickness (S2)           | 0.25 mm |
| Stripping length            | 10 mm                | Wire connection cross section AWG, max. | AWG 18  |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000005    | ETIM 4.0   | EC000005    |
| ETIM 5.0   | EC000005    | ETIM 6.0   | EC000005    |
| UNSPSC     | 31-16-31-02 | eClass 5.1 | 27-40-02-01 |
| eClass 6.2 | 27-40-02-01 | eClass 7.1 | 27-40-02-01 |
| eClass 8.1 | 27-40-02-01 | eClass 9.0 | 27-40-02-01 |
| eClass 9.1 | 27-40-02-01 |            |             |

### Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |                                      |
|--------------------|--------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 6 TOOLS 15/16 EN</a> |
| Engineering Data   | <a href="#">EPLAN</a>                |
| Engineering Data   | <a href="#">STEP</a>                 |

### Connecting elements H0,75/14DS GR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Similar to illustration

