


## Connecting elements H1,0/15 ZH GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

### General ordering data

|            |                                                              |
|------------|--------------------------------------------------------------|
| Type       | H1,0/15 ZH GE                                                |
| Order No.  | <a href="#">9037260000</a>                                   |
| Version    | Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, yellow |
| GTIN (EAN) | 4008190492731                                                |
| Qty.       | 500 pc(s).                                                   |
| Packaging  | loose                                                        |

## Connecting elements

### H1,0/15 ZH GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |        |                |            |
|------------|--------|----------------|------------|
| Width      | 15 mm  | Width (inches) | 0.591 inch |
| Net weight | 0.13 g |                |            |

### Technical data

|         |                       |
|---------|-----------------------|
| Version | Twin wire-end ferrule |
|---------|-----------------------|

### Wire-end ferrules

|                                         |            |                             |                   |
|-----------------------------------------|------------|-----------------------------|-------------------|
| Collar height (A)                       | 5.8 mm     | Collar width (B)            | 3.2 mm            |
| Colour code                             | Weidmüller | Conductor cross-section     | 1 mm <sup>2</sup> |
| Contact surface diameter (D1)           | 2 mm       | Contact surface length (L2) | 8 mm              |
| L1 in mm                                | 15 mm      | Metal sleeve thickness (S1) | 0.15 mm           |
| Plastic collar thickness (S2)           | 0.3 mm     | Stripping length            | 11 mm             |
| Wire connection cross section AWG, max. | AWG 17     |                             |                   |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000005    | ETIM 4.0   | EC000005    |
| ETIM 5.0   | EC000005    | ETIM 6.0   | EC000005    |
| UNSPSC     | 31-16-31-02 | eClass 5.1 | 27-40-02-01 |
| eClass 6.2 | 27-40-02-01 | eClass 7.1 | 27-40-02-01 |
| eClass 8.1 | 27-40-02-01 | eClass 9.0 | 27-40-02-01 |
| eClass 9.1 | 27-40-02-01 |            |             |

### Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |                                          |
|--------------------|------------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 6 TOOLS 15/16 EN</a>     |
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a> |
| Engineering Data   | <a href="#">STEP</a>                     |

### Connecting elements H1,0/15 ZH GE

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Similar to illustration

