

**Smoke Detector Test Spray****! SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier**

**Name of product** Smoke Detector Test Spray  
Code-Nr. 116402

**1.2. Relevant identified uses of the substance or mixture and uses advised against  
Recommended intended purpose(s)**

Technical Aerosols

**1.3. Details of the supplier of the safety data sheet****Distributor**

WEICON GmbH & Co. KG  
Königsberger Str. 255, DE-48157 Münster  
Postbox 48045, DE-8460 Münster  
Phone ++49(0)251 / 9322 - 0, Fax ++49(0)251 / 9322 - 244  
E-Mail : msds@weicon.de  
Internet : www.weicon.de

**Advice**

Produktsicherheit / Product-Safety-Department  
Phone ++49(0)251 / 9322 - 0  
E-mail (competent person):  
msds@weicon.de

**1.4. Emergency telephone number**

GIZ Bonn (German, English) Tel: ++49(0)228-19 240  
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178  
433 7434 (24h Emergency Contact)

**Manufacturer**

WEICON GmbH & Co. KG  
Königsberger Str. 255, DE-48157 Münster

**1.4. Emergency telephone number****Emergency advice**

-  
Phone -  
GIZ Bonn (Medizinische Auskunft in Deutsch und Englisch)  
Tel: ++49(0)228-19 240  
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178  
433 7434 (24h Emergency Contact)

**! SECTION 2: Hazards identification****2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]**

Hazard classes and Hazard categories	Hazard Statements	Classification procedure
--------------------------------------	-------------------	--------------------------

Aerosol 1	H222, H229	
Eye Irrit. 2	H319	
STOT SE 3	H336	

**Hazard Statements**

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.

H319 Causes serious eye irritation.  
 H336 May cause drowsiness or dizziness.

## 2.2. Label elements

### Labelling according to Regulation (EC) No 1272/2008 [CLP/GHS]



GHS02



GHS07

### Signal word

Danger

### Hazard Statements

H222 Extremely flammable aerosol.  
 H229 Pressurised container: May burst if heated.  
 H319 Causes serious eye irritation.  
 H336 May cause drowsiness or dizziness.

### Precautionary Statements

P102 Keep out of reach of children.  
 P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
 P211 Do not spray on an open flame or other ignition source.  
 P251 Do not pierce or burn, even after use.  
 P261 Avoid breathing dust/fume/gas/mist/vapours/spray.  
 P264 Wash hands thoroughly after handling.  
 P271 Use only outdoors or in a well-ventilated area.  
 P280 Wear protective gloves/protective clothing/eye protection/face protection.  
 P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.  
 P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
 P312 Call a POISON CENTER or doctor/physician if you feel unwell.  
 P337 + P313 If eye irritation persists: Get medical advice/attention.  
 P403 + P235 Store in a well-ventilated place. Keep cool.  
 P405 Store locked up.  
 P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.  
 P501 Dispose of contents/container to hazardous or special waste collection point.

### 2.3. Other hazards

Product has an anesthetic effect.

### ! Information pertaining to special dangers for human and environment

In extensive use, formation of flammable / explosive vapour-air mixture is possible.

### Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

**! SECTION 3: Composition/ information on ingredients****3.1. Substances**

not applicable

**3.2. Mixtures****Description**

Mixture of active ingredients with propellant

**Hazardous ingredients**

CAS No	EC No	Name	[%]	Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]
67-63-0	200-661-7	propan-2-ol	10-19,99	Flam. Liq. 2, H225 / Eye Irrit. 2, H319 / STOT SE 3, H336
74-98-6	200-827-9	propane	10 - 20	Flam. Gas 1, H220 / Press. Gas
75-28-5	200-857-2	isobutane	10 - 20	Flam. Gas 1, H220 / Press. Gas
106-97-8	203-448-7	butane	50-70	Flam. Gas 1, H220 / Press. Gas

**REACH**

CAS No	Name	REACH registration number
67-63-0	propan-2-ol	01-2119457558-25

**SECTION 4: First aid measures****4.1. Description of first aid measures****General information**

Remove contaminated soaked clothing immediately.

**In case of inhalation**

Ensure of fresh air.

In the event of symptoms refer for medical treatment.

**In case of skin contact**

Consult a doctor if skin irritation persists.

**In case of eye contact**

In case of contact with eyes rinsing with plenty of lukewarm water carefully and seek for medical treatment.

**In case of ingestion**

Seek medical advice.

**4.2. Most important symptoms and effects, both acute and delayed**

No information available.

**4.3. Indication of any immediate medical attention and special treatment needed**

No information available.

**SECTION 5: Firefighting measures****5.1. Extinguishing media****Suitable extinguishing media**

Alcohol-resistant foam

Dry powder

Carbon dioxide

Water spray jet



## Smoke Detector Test Spray

### 5.2. Special hazards arising from the substance or mixture

Danger of bursting

In case of fire formation of dangerous gases possible.

### 5.3. Advice for firefighters

#### Special protective equipment for fire-fighters

Fire-fighting operations, rescue and clearing work under effect of combustion and smoulder gases just may be done with breathing apparatus.

#### Additional information

Cool endangered containers with water spray jet.

Collect contaminated firefighting water separately, must not be discharged into the drains.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

#### For non-emergency personnel

Ensure adequate ventilation.

Use personal protective clothing.

Keep away sources of ignition.

### 6.2. Environmental precautions

Do not discharge into the drains/surface waters/groundwater.

### 6.3. Methods and material for containment and cleaning up

Allow to vaporise.

#### Additional Information

Sort out leaky cans and dispose according to regulations.

### 6.4. Reference to other sections

Safe handling: see section 7

Disposal: see section 13

Personal protection equipment: see section 8

## ! SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

#### ! Advice on safe handling

Care for thoroughly room ventilation, if necessary use in well ventilated area with local exhaust ventilation at workplace.

#### ! General protective measures

Do not inhale gases/vapours/aerosols.

Ensure sufficient ventilation.

#### Hygiene measures

At work do not eat, drink and smoke.

Wash hands before breaks and after work.

#### Advice on protection against fire and explosion

Do not spray on a naked flame or any incandescent material.

Pressurized container.

Do not pierce or burn even after use.

Vapours can form an explosive mixture with air.

Avoid effect of heat.

**Smoke Detector Test Spray****7.2. Conditions for safe storage, including any incompatibilities****Requirements for storage rooms and vessels**

Keep in closed original container.

Adhere to administrative regulations relating to storage of compressed gas cylinders / containers.

**Further information on storage conditions**

Protect from heat and direct solar radiation.

Keep container dry and store at cool and aired place.

**7.3. Specific end use(s)****Recommendation(s) for intended use**

See section 1.2

**! SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Ingredients with occupational exposure limits to be monitored**

CAS No	Name	Code	[mg/m3]	[ppm]	Remark
106-97-8	Butane	8 hours	1450	600	EH40/2005
		Short-term	1810	750	

**Additional advice**

The statutory local and national regulations have to be observed.

**8.2. Exposure controls****Respiratory protection**

In case of insufficient ventilation or long-term effect use breathing apparatus.

**Hand protection**

In the cases of special applications, it is recommended to check the chemical resistance with the manufacturer of the gloves.

Glove material specification [make/type, thickness, permeation time/life, wetting resistance]: Nitrile rubber; 0,4mm; 480min;60min.

**! Eye protection**

tightly fitting goggles

**Other protection measures**

protective clothing

**Appropriate engineering controls**

Care for thoroughly room ventilation, if necessary use in well ventilated area with local exhaust ventilation at workplace.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties****Appearance**

aerosol

**Colour**

colourless

**Odour**

characteristic

**Odour threshold**

not determined

**Important health, safety and environmental information**

	Value	Temperature	at	Method	Remark
pH value	not determined				



## Safety Data Sheet according to Regulation (EC)

No. 1907/2006 (REACH)

Printed 11.01.2016

revision 18.06.2015 (GB) Version 8.3

**Smoke Detector Test Spray**

	Value	Temperature	at	Method	Remark
<b>boiling point</b>	not applicable				
<b>Melting point / Freezing point</b>	not determined				
<b>Flash point</b>	not applicable				Aerosol
<b>Vapourisation rate</b>	not determined				
<b>Flammable (solid)</b>	not applicable				
<b>Flammability (gas)</b>	not determined				
<b>Ignition temperature</b>	365 °C				
<b>Self ignition temperature</b>					The product is not self-igniting.
<b>Lower explosion limit</b>	1,5 %				
<b>Upper explosion limit</b>	12 %				
<b>Vapour pressure</b>	4400 hPa	20 °C			
<b>Relative density</b>	0,59 g/cm <sup>3</sup>	20 °C			
<b>Vapour density</b>	not determined				
<b>Solubility in water</b>					miscible
<b>Solubility/other</b>	not determined				
<b>Partition coefficient n-octanol/water (log P O/W)</b>	not determined				
<b>Decomposition temperature</b>	not determined				
<b>Viscosity dynamic</b>	not determined				
<b>Viscosity kinematic</b>	not determined				

**Oxidising properties**

No information available.

**Explosive properties**

The product is considered non-explosive ; nevertheless explosive vapour/air mixtures can be generated .

**9.2. Other information**

No information available.



---

**SECTION 10: Stability and reactivity****10.1. Reactivity**

No information available.

**10.2. Chemical stability**

No information available.

**10.3. Possibility of hazardous reactions**

No information available.

**10.4. Conditions to avoid**

Keep away from heat.

Formation of explosive gas/air mixtures.

**10.5. Incompatible materials**

No information available.

**10.6. Hazardous decomposition products****Thermal decomposition**

Remark No decomposition if used as directed.

---

**SECTION 11: Toxicological information****11.1. Information on toxicological effects****Acute toxicity/Irritation/Sensitization**

	Value/Validation	Species	Method	Remark
<b>Skin irritation</b>	non-irritant			
<b>Eye irritation</b>	irritant			
<b>Skin sensitization</b>	non-sensitizing			

**Additional information**

The product is to be handled with the caution usual with chemicals.

Other hazardous properties may not be excluded.

---

**SECTION 12: Ecological information****12.1. Toxicity**

No information available.

**12.2. Persistence and degradability**

No information available.

**12.3. Bioaccumulative potential**

No information available.

**12.4. Mobility in soil**

No information available.

**12.5. Results of PBT and vPvB assessment**

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

**12.6. Other adverse effects**

**Smoke Detector Test Spray****General regulation**

Do not allow uncontrolled leakage of product into the environment.

**SECTION 13: Disposal considerations****13.1. Waste treatment methods****Waste code No.**

15 01 04

15 01 10\*

**Name of waste**

metallic packaging

packaging containing residues of or contaminated by hazardous substances

Wastes marked with an asterisk are considered to be hazardous waste pursuant to Directive 2008/98/EC on hazardous waste.

**Recommendations for the product**

Remove in accordance with local official regulations.

**Recommendations for packaging**

Totally emptied packaging may be treated as household waste.

**Recommended cleansing agent**

Water

**General information**

For proper waste disposal a complete emptying of the tin is necessary.

**! SECTION 14: Transport information**

	<b>ADR/RID</b>	<b>IMDG</b>	<b>IATA-DGR</b>
<b>14.1. UN number</b>	1950	1950	1950
<b>14.2. UN proper shipping name</b>	AEROSOLS	AEROSOLS	Aerosols, flammable
<b>14.3. Transport hazard class(es)</b>	2.1	2.1	2.1
<b>14.4. Packing group</b>	-	-	-
<b>14.5. Environmental hazards</b>	No	No	No

**14.6. Special precautions for user**

Caution: Gases

**14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code**

not applicable

**Land and inland navigation transport ADR/RID**

Hazard label(s) 2.1

tunnel restriction code D

Classification code 5F

**! Transport/further information**

24h EMERGENCY CONTACT (TRANSPORT) +49(0)178 433 7434 (Consultank Lutz Harder GmbH)





---

## ! SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### ! VOC standard

VOC content 99,5 %

VOC value 589 g/L

### 15.2. Chemical Safety Assessment

Chemical safety assessments for substances in this mixture were not carried out.

---

## ! SECTION 16: Other information

### ! Recommended uses and restrictions

National and local regulations concerning chemicals shall be observed.

For industrial use only.

### Further information

Each user is responsible for the implementation of the national special regulations.

The information contained herein is based on the state of our knowledge. It characterizes the product with regard to the appropriate safety precautions. It does not represent a guarantee of the properties of the product.

Please observe the following disclaimer! --- Our safety data sheets have been compiled according to effective EU-directives, WITHOUT taking into account the special national directives concerning the handling of hazardous substances.

Indication of changes: "!" = Data changed compared with the previous version. Previous version: 8.2

H220 Extremely flammable gas.  
H225 Highly flammable liquid and vapour.  
H319 Causes serious eye irritation.  
H336 May cause drowsiness or dizziness.