

## RS-SERIES

### RS 32 24VDC LD LP 2U

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

### Product image



Clip-on RS 30. 31. 32 relay bases are available in widths from 11.2 to 25 mm, depending on the type.

The RSM relay multiplexers are available as 4, 8 and 16-way modules. To reduce the wiring work, the DC variants are fitted with a common plus or minus potential. The optional IEC603-1 plug-in connector enables the connection of pre-assembled lines.

The screw connection system is used to connect the conductor with a rated cross-section of 2.5 mm<sup>2</sup>.

### General ordering data

Type	RS 32 24VDC LD LP 2U
Order No.	<a href="#">9406121001</a>
Version	RS-SERIES, Relays, No. of contacts: 2 CO contact AgNi 90/10, Rated control voltage: 24 V DC ±10 %, Continuous current: 4 A, Screw connection
GTIN (EAN)	4008190027193
Qty.	10 pc(s).

**RS-SERIES**  
**RS 32 24VDC LD LP 2U**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	25 mm	Width (inches)	0.984 inch
Height	70 mm	Height (inches)	2.756 inch
Depth	63.5 mm	Depth (inches)	2.5 inch
Net weight	44.88 g		

**Temperatures**

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature, max.	40 °C
Operating temperature, min.	-25 °C	Storage temperature, max.	60 °C
Storage temperature, min.	-40 °C	Operating temperature	-25 °C...40 °C
Storage temperature	-40 °C...60 °C		

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Input**

Rated control voltage	24 V DC $\pm$ 10 %	Rated current DC	25 mA
Power rating	0.6 W	Pull-in/drop-out voltage, typ.	21.5 V DC
Pull-in/drop-out current, typ.	5 mA DC	Status indicator	red LED
Protective circuit	Free-wheeling diode, Reverse polarity protection		

**Output**

Rated switching voltage	250 V AC	Max. switching voltage, AC	250 V
Continuous current	4 A	Inrush current	6 A
Switch-on delay	< 13 ms	Switch-off delay	= 10 ms
Duration of Bounce	$\leq$ 4 ms	Min. switching power	1 mA @ 24 V, 10 mA @ 10 V, 100 mA / 5 V DC
Max. switching frequency at rated load	0.1 Hz		

**Contact data**

Contact type	2 CO contact (AgNi 90/10)	Mechanical service life	30 x 10 <sup>6</sup> switching cycles
--------------	------------------------------	-------------------------	---------------------------------------

**General data**

Version	soldered relay	Rail	TS 32, TS 35
Test button	No	Mechanical switch position indicator	No
Colour	orange		

**Insulation coordination**

Rated voltage	250 V	Surge voltage category	III
Pollution severity	2	Protection degree	IP20
Creepage and clearance distance input - output	> 3 mm	Impulse withstand voltage	4 kV

**Further details of approvals / standards**

Standards DIN EN 50178

Creation date May 28, 2019 3:16:24 PM CEST

**Data sheet**

**RS-SERIES  
RS 32 24VDC LD LP 2U**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Connection data**

Wire connection method	Screw connection	Stripping length, rated connection	8 mm
Clamping range, rated connection	2.5 mm <sup>2</sup>	Clamping range, min.	0.5 mm <sup>2</sup>
Clamping range, max.	4 mm <sup>2</sup>		

**Classifications**

ETIM 3.0	EC001437	ETIM 4.0	EC001437
ETIM 5.0	EC001437	ETIM 6.0	EC001437
UNSPSC	30-21-19-17	eClass 5.1	27-37-16-01
eClass 6.2	27-37-16-01	eClass 7.1	27-37-16-01
eClass 8.1	27-37-16-01	eClass 9.0	27-37-16-01
eClass 9.1	27-37-16-01		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">DE_PA_5600_160311_001.pdf</a>
Engineering Data	<a href="#">EPLAN.WSCAD</a>

**Data sheet****RS-SERIES  
RS 32 24VDC LD LP 2U**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings****Wiring diagram**