

Residual current monitor RCMA420

AC/DC sensitive residual current monitor for TN and TT systems (AC, DC and pulsed DC currents)



Device features

- AC / DC sensitive residual current monitor Type B acc. to IEC 62020 and IEC/TR 60755
- r.m.s. value measurement (AC+DC)
- Two separately adjustable response values 10...500 mA
- Frequency range 0...2000 Hz
- Start-up delay, response delay and delay on release
- Digital measured value display via LC display
- Measured value memory for operating value
- CT connection monitoring
- Power On LED, LEDs: Alarm 1 / 2
- Internal/external test/reset button
- Two separate alarm relays (one changeover contact each)
- N/O or N/C operation and fault memory behaviour selectable
- · Continuous self monitoring
- Multi-functional LC display
- · Password protection for device settings
- · Sealable transparent cover
- Two-module enclosure (36 mm)
- RoHS compliant
- Push-wire terminal (two terminals per connection)

Approvals and certifications







Product description

The AC/DC sensitive residual current monitor RCMA420 is designed for monitoring earthed power supply systems (TN and TT systems) where smooth DC fault currents or residual currents continuously greater than zero may occur. These are in particular loads containing six-pulse rectifiers or one way rectifiers with smoothing, such as converters, battery chargers, construction site equipment with frequency-controlled drives. Currents in single conductors can be monitored too.

The prewarning stage (50...100 % of the set response value $I_{\Delta n2}$) allow to distinguish between prewarning and alarm. Since the values are measured with measuring current transformers, the device is nearly independent of the load current and the nominal voltage of the system.

Applications

- AC/DC sensitive residual current monitoring in earthed two, three or four conductor systems (TN and TT systems)
- Monitoring of variable-speed drives, UPS systems, construction site equipment, printing machines, battery systems, laboratory equipment, wood working machines, MF welding systems, furniture industry, medical electrical equipment, etc.
- AC/DC sensitive current monitoring of single conductors de-energised under normal conditions (e.g. N and PE conductors)

Function


Once the supply voltage U_S is applied, the start-up delay is activated. Measured values changing during this time do not influence the switching state of the alarm relays.

Residual current measurement takes place via an external measuring current transformer of the W20AB...W60AB series. The currently measured value is shown on the LC display. In this way any changes, for example when circuits are connected to the system, can be recognised easily. If the measured value exceeds the set response values, the response delays $t_{\rm on1/2}$ begin. Once the response delay $t_{\rm on1/2}$ has elapsed, the K1/K2 alarm relays switch and the alarm LEDs AL1/AL2 light up. If the current falls below the release value (response value plus hysteresis), the release delay $t_{\rm off}$. When toff has elapsed, the alarm relays return to their initial position and the alarm LEDs AL1/AL2 go out. If the fault memory is activated, the alarm relays remain in the alarm state and the LEDs light until the reset button is pressed or until the supply voltage is interrupted. The device function can be tested using the test button. Parameters are assigned to the device via the LCD and the control buttons on the front panel; this function can be password-protected.


Connection monitoring

The function of the device and the CT connections are continuously monitored. In the event of a fault, the alarm relays K1 / K2 switch without delay, the alarm LEDs AL1 / AL2 / ON flash. On removal of the fault, the alarm relays return to their initial position either automatically or by pressing the reset button.






Operating and display elements



- 1 Power On LED "ON" (green); lights when supply voltage is applied and flashes in the event of system fault alarm respectively in the event of CT malfunction.
- **2** Alarm LED "AL1" (yellow), prewarning; lights when the set response value $I_{\Delta n1}$ is exceeded or flashes in the event of system fault alarm respectively in the event of CT malfunction
- 3 Alarm LED "AL2" (yellow), alarm; lights when the set response value $I_{\Delta n2}$ is exceeded or flashes in the event of system fault alarm respectively in the event of CT malfunction
- 4 Multi functional LC display
- 5 Test button "T": to call up the self test.Arrow up button: parameter change, to move up in the menu
- 6 Reset button "R": to delete saved alarms.Down button: parameter change, to move down in the menu
- 7 "MENU" button: to call up the menu system. Enter button: to confirm parameter change. Press ESC: press the button > 1.5 seconds.

Wiring diagram





- Supply voltage U_S see ordering information (6 A fuse recommended)
- Connector for the external W20AB...W60AB series measuring current transformer
- 3 Alarm relay K1: $I_{\Delta n1}$ (prewarning)
- **4** Alarm relay K2: alarm $I_{\Delta n2}$ (alarm)
- 5 Combined test and reset button "T/R" short-time pressing (< 1.5 s) = RESET long-time pressing (> 1.5 s) = TEST

Do not route the PE conductor through the measuring current transformer!



Connection of measuring current transformers






Connection to the RCMA420 residual current monitor using the WX-... connecting cable.

Colour coding for WX...: k = yellow, l = green, -12 V = black, GND = brown, +12 V = red, Test (T) = orange

Dimension diagram XM420


Dimensions in mm

Open the front plate cover in direction of arrow!



Screw mounting

Note: The upper mounting clip must be ordered separately (see ordering information).



Ordering information					
Туре	Response range I∆n	Frequency range	Supply voltage <i>U</i> s*	Art. No.	
RCMA420-D-1	10500 mA	02000 Hz	DC 9.694 V / AC 42460 Hz 1672 V	B 7404 3001	
RCMA420-D-2	10500 mA	02000 Hz	DC 70300 V / AC 42460 Hz / 70300 V	B 7404 3002	

Device version with screw terminals on request. * Absolute values

Measuring current transformers			
Туре	Internal diameter (mm)	Art. No.	
W20AB	ø 20	B 9808 0008	
W35AB	ø 35	B 9808 0016	
W60AB	ø 60	B 9808 0026	

Connection cable measuring current transformer – RCMA420-D			
Туре	Length/m	Art. No.	
WX-100	1	B 9808 0503	
WX-250	2.5	B 9808 0504	
WX-500	5	B 9808 0505	
WX-1000	10	B 9808 0506	

Accessories	
Туре	Art. No.
Mounting clip for XM420 enclosure	B 9806 0008
Snap-on mounting W20, W35	B 9808 0501
Snap-on mounting W60	B 9808 0502

(1 unit required for each device)



Technical data

Insulation coordination acc. to IEC 60664-1/IEC 606	64-3
Rated insulation voltage	250 V
Rated impulse voltage/pollution degree	2.5 kV / III
Protective separation (reinforced insulation) between	
	I, T/R) - (11, 12, 14) - (21, 22, 24)
Voltage tests according to IEC 61010-1	2.21 kV
Supply voltage	
RCMA420-D-1:	
Supply voltage <i>U</i> s	AC 1672 V / DC 9.694 V
Frequency range Us	42460 Hz
RCMA420-D-2:	
Supply voltage U_S	AC/DC 70300 V
Frequency range Us	42460 Hz
Power consumption	≤ 3 VA
Measuring circuit	
External measuring current transformer	W20AB, W35AB, W60AB series
Rated insulation voltage (measuring current transformer)	
Operating characteristic acc. to IEC 62020 and IEC/TR 6075	
Rated frequency	02000 Hz
Measuring range AC	01.5 A
Measuring range DC	0600 mA
Relative uncertainty of the response value	035%
Relative uncertainty	035%
Response values	
Rated residual operating current $I_{\Delta n1}$ (prewarning, AL1)	50100 % x /Δn2, (50 %)*
Rated residual operating current $I_{\Delta n2}$ (alarm, AL2)	10500 mA (30 mA)*
Hysteresis	1025 % (15 %)*
Specified time	
Start-up delay t	010 s (0.5 s)*
Response delay t _{on2} (alarm)	010 s (0.s)*
Response delay t _{on1} (prewarning)	010 s (1 s)*
Delay on release t_{off}	099 s (1 s)*
Operating time t_{ae} at $I_{\Delta n} = 1 \times I_{\Delta n 1/2}$	≤ 180 ms
Operating time t_{ae} at $I_{\Delta n} = 5 \times I_{\Delta n 1/2}$	< 30 ms
Response time t _{an}	$t_{\rm an} = t_{\rm ae} + t_{\rm on 1/2}$
Recovery time t _b	< 300 ms
Cable lengths for measuring current transformers	_ 500
	le WX 1 m / 2.5 m / 5 m / 10 m
	ic wx 1 iii / 2.5 iii / 5 iii / 10 iii
Displays, memory	Λ 1ΓΛ
Display range, measured value AC Display range, measured value DC	01.5 A
Display range, measured value DC Error of indication	0600 mA
	\pm 17,5 % / \pm 2 digit data record measured values
Measured-value memory for alarm value	
Password Fault memory alarm relay	off / 0999 (off)* on / off (on)*
I auit ilicilluly alailii lelay	011 / 011 (011)"

Cable length for external test/reset butto	on			0	10 m
Switching elements					
Number of switching elements				angeove	
Operating principle	N/C operati	on / N/O	operation	(N/C ope	ration)*
Electrical endurance, number of cycles					10000
Contact data acc. to IEC 60947-5-1					
Utilisation category	AC-13	AC-14	DC-12	DC-12	DC-12
Rated operational voltage	230 V	230 V	24 V	110 V	220 V
Rated operational current	5 A	3 A	1 A	0.2 A	0.1 A
Minimum contact rating			1 m/	A at AC/D	C ≥ 10 V
Environment/EMC					
EMC				IE	C 62020
Operating temperature				-25 °C	.+55 º(
Climatic class acc. to IEC 60721					
Stationary use (IEC 60721-3-3)	3K5 (except	condens	ation and	l formatio	n of ice
Transport (IEC 60721-3-2)	2K3 (except	condens	ation and	l formatio	n of ice
Long-time storage (IEC 60721-3-1)	1K4 (except	condens	ation and	l formatio	n of ice
Classification of mechanical conditions IE	C 60721				
Stationary use (IEC 60721-3-3)					3M
Transport (IEC 60721-3-2)					2M
Long-time storage (IEC 60721-3-1)					1M:
Connection					
Connection type			pu	sh-wire t	erminal
Connection properties					
rigid		0	.22.5 r	mm² / AW	/G 24-12
flexible without ferrule		-	.22.5 r	,	
flexible with ferrule		0	.21.5 r	mm² / AW	/G 24-1
Stripping length					10 mn
Opening force					501
Test opening, diameter					2.1 mn
Other .					
Operating mode			con	tinuous o	peratio
Position of normal use				display-	oriente
Degree of protection, internal componer	nts (IEC 60529)	1			IP3
Degree of protection, terminals (IEC 605)					IP2
Enclosure material				polyca	rbonat
Flammability class				. ,	UL94V-
DIN rail mounting acc. to				IE	C 6071
Screw fixing			2 x M4 w	ith moun	ting cli
Software version					42 V1.1
On a wating manual				-	C111.41

()* = factory setting

Operating manual

Weight

TGH1411

≤ 150 g