MAGLITE® MAG-TAC®

Crowned Bezel



Crowned Bezel
Plain Bezel

Designed with extensive input from military tactical consultants, yet suitable also for civilian use, the crowned-bezel version of the MAG-TAC® LED flashlight comes with a detachable pocket clip and features three modes: Momentary (in which the light stays on only while the switch button is being pressed); Full Power for a dazzling, 320-lumen beam that can light up an object two football fields away; and Strobe for a high-energy 12 Hz strobe that can disorient an opponent. All functions are selectable through Mag Instrument's tail capswitch-activated "QuickClikTM" mode selector.

Plain Bezel

Designed with extensive input from police tactical users, yet suitable also for civilian use, this plain-bezel version of the MAG-TAC® LED flashlight comes with a detachable pocket clip and features three modes: Two power levels (Full Power for extreme brightness and Power Save for prolonged battery life) plus a Momentary mode (in which the light stays on only while the switch button is being pressed) all selectable through Mag Instrument's tail cap-switch-activated "QuickClik™" mode selector.

Packaging Options



Blister pack

Features & Benefits









Available Colors







Black Foliage Green

Urban Gray

TECHNICAL SPECIFICATIONS



2m

Crowned 2-Cell CR123

- Type Tactical
- Lumens 320 Im
- Beam Distance 193m
- Peak Beam Intensity 9267cd
- Barrel Diameter 1.050 in. / 26.67 mm
- Batteries (CR123) Included
- Weight With Batteries 4.8 oz. / 136g
- Water-Resistant Yes
- Drop Resistance 2m
- Technology LED
- Length 5.275 in. / 133.98 mm
- Run Time, High 4h
- Head Diameter 1.050 in. / 26.67 mm
- Rechargeable No
- Blister Size 8.88 H x 4.88 W x 1.38 D in.



Plain 2-Cell CR123

- Type Tactical
- Lumens 310 Im
- Beam Distance 182m
- Peak Beam Intensity 8293cd
- Barrel Diameter 1.050 in. / 26.67 mm
- Batteries (CR123) Included
- Weight With Batteries 4.8 oz. / 136g
- Water-Resistant Yes
- Drop Resistance 2m
- Technology LED
- Length 5.203 in. / 132.16 mm
- Run Time, High/Low 4h/17h
- Head Diameter 1.050 in. / 26.67 mm
- Rechargeable No
- Blister Size 8.88 H x 4.88 W x 1.38 D in.



MAG INSTRUMENT, INC. • 2001 South Hellman Ave., Ontario, CA 91761 909-947-1006 • 800-289-6241 • www.maglite.com • email: salesdesk@magmail.com



