


Pigtail set SC/PC OS2 9/125μ, 12 Different Colours , 2M

Blue,Orange,Green,Brown,Slate,White,Red,Black,Yellow,Violet,Rose,Aqua

(900μ m and 250μ m are same Color)



Characteristics:

1. Insertion Loss: $\leq 0.3\text{dB}$ @1310nm
Return Loss: $\geq 55\text{dB}$ @1310nm
2. End surface test is according to OP-03-05001
3. Test standard: GR-326-CORE
4. Test report has to match the serial-no
5. RoHS compliant
6. Fiber cable according to IEC 60793-2
7. SC Connector according to IEC 61754-4

RoHS
Compliant

4	Ø0.9mm SM 9/125μm OS2 12 Different Colours Jacket Cable		
3	SC 0.9mm Boot,Blue	1	PCS
2	SC/PC Connector,Blue	1	PCS
1	SC Dust Cover	1	PCS
No.	Description	Q'TY	Unit



EFB

Pigtail set SC/PC OS2 9/125μ, 12 Different Colours , 2M

Part No.: O1022.2

Drawing No.:



Page : 1 of 3

Packing

The corresponding label data for each cable assembly shall be glued to the package

Front

Back




Prüfprotokoll inspection sheet Typ: O1022.2 Stückzahl 12 quantity 12
Einfügedämpfung nach DIN 18600 Verfahren 7 insertion loss acc. to DIN 18600 mode 7 Wellenlänge 1310 nm Steckerdämpfung <0.3dB wellenlänge 1310 nm insertion loss <0.3dB 9/125 Date: 2011-09-13 Achtung LWL Komponenten attention fiber optic cable
-Vorsichtig handhaben handle with care -Mindestbiegeradius von 40mm nicht unterschreiten do not decrease bending radius of 40mm -Stecken u.Lösen der Verbindung nur durch Handhabung am Steckergehäuse Ensure to use only connector body for connection/disconnection Nicht am Kabel ziehen!!! never pull at fiber optic cables!!! -Reklamationen in diesem Bereich können wir nicht anerkennen complaints in this regard cannot be accepted -Ferrulen stets durch Staubschutzkappe schützen und vor jedem Einsatz säubern ferrules must be protected via dust covers and must be cleaned before use

Test Report

Bar Code Label

9# PE Bag (220mm X 280mm)

Pigtail Set SC/PC OS2 9/125µ 12 Different colours, 2 M			
Part Number: O1022.2		Quantity: 12 pcs	
SC/PC			
IL: 0.08 dB	RL: 60 dB	IL: 0.07 dB	RL: 57 dB
IL: 0.10 dB	RL: 58 dB	IL: 0.10 dB	RL: 60 dB
IL: 0.12 dB	RL: 57 dB	IL: 0.11 dB	RL: 59 dB
IL: 0.07 dB	RL: 59 dB	IL: 0.07 dB	RL: 60 dB
IL: 0.10 dB	RL: 60 dB	IL: 0.09 dB	RL: 58 dB
IL: 0.07 dB	RL: 59 dB	IL: 0.08 dB	RL: 60 dB
Bar Code: 			
Batch: 20110913			

Bar Code Label (100mm X 60mm)

Achtung
Lichtwellenleiter!
Bei unsachgemäßer
Handhabung entfallen
Haftungsansprüche!

Label

RoHS
Compliant



E.F.B.

Pigtail set SC/PC OS2 9/125µ, 12 Different Colours , 2M

Part No.: O1022.2

Drawing No.:

Page : 2 of 3

1. Characteristics

- . Small outer diameter, lightweight
- . Flame-retardant jacket, halogen free
- . Low attenuation
- . Easy to strip

2. Applications

- . Installation in conduits and shafts
- . Indoor distribution
- . Spliced Connections
- . Connecting workstations inside buildings(FTTD)

3. Temperature Range


- . -20° C up to + 70° C

4. Fiber Optic Cable Performance:

- . Number of fibers: 1
- . Outside diameter: 0.9mm
- . Nominal weight: 0.9kg/km
- . Max. tension:6.0N(short-term)
3.0N(long-term)
- . Min. Bending Radius:20D(Dynamic)
10D(Static)
- . Complies with TIA/EIA568 B.3 & Bellcore GR-409-CORE & OFNR-UL/CSA FT-4
- . Max. Attenuation(typ.): $\leq 0.4\text{dB}$ (full spectrum)
- . Dispersion Coefficient: $\leq 3.0\text{ps}/(\text{nm}\cdot\text{km})$ @1310nm
 $\leq 18\text{ps}/(\text{nm}\cdot\text{km})$ @1550nm

5. Cable Specification

- . Fiber type: SM 9/125 μ OS2
- . LSZH Jacket , Blue,Orange,Green,Brown,Slate,White,Red,Black,Yellow, Violet,Rose,Aqua (900 μm and 250 μm are same Color)



(900 μm and 250 μm are same Color)

RoHS
Compliant



E/FB

Pigtail set SC/PC OS2 9/125 μ , 12 Different Colours , 2M

Part No.: O1022.2

Drawing No.:

Page : 3 of 3