

Customer: ALPS EUROPE DISTRIBUTION

No. KK-2007-2700

Date: Jan. 30, 2007

Attention:

Your ref. No.:

Your Part No.: RK27112MC01L

SPECIFICATIONS

ALPS' ;

MODEL: RK27112MC01L
(100kBX2)

Spec. No.:

Sample No.: F 3 7 3 8 0 5 8 M

RECEIPT STATUS

RECEIVED

By Date

Signature

Name

Title

ALPS[®]
ALPS ELECTRIC CO., LTD.

Head Office

1-7, Yukigaya-otsuka-cho, Ota-ku, Tokyo, 145-8501 Japan
Phone,+81(3)3726-1211

DSG'D

Y. Ohya

APP'D

S. Ikenoue

ENG. DEPT. DIVISION

Sales

B6523

Q1003#03A (EA)

SPECIFICATIONS

1. THIS SPECIFICATIONS APPLY TO RK27112MC01L POTENTIOMETER.

2. CONTENTS OF THIS SPECIFICATIONS.

5K272AMS-5

K272AMC02C

4K16M-1

4K-1

3. MARKING

- MARKING ON ALL UNITS
DATE CODE, RESIST. VALUE, TAPER

4. REMARKS

- FURNISH PACKAGE
NUT:1 WASHER:1

• NOTES

- Silver printed patterns are coated with carbon as a protection against sulphuration.
- Marking ⇒ in specifications shows standard and condition for application.

• CAUTION

Regardless of the suggested applications of these products being introduced in the specifications, when using them for equipment and devices requiring a high degree of safety, respective manufacturers will please preserve safety of the planned equipment and devices by providing necessary protective circuits and redundancy circuits and reconfirm if safety is being duly preserved.

Products being introduced in the specifications have been designed and manufactured for applications to ordinary electronic equipment and devices such as the AV equipment, electric home appliances, office machines and communications equipment. Consequently, when employing these products for applications requiring a high degree of safety and reliability such as the medical equipment, aviation and aircraft equipment, space equipment and burglar alarm equipment, the using manufacturers will please thoroughly study the proprieties of these products for the planned applications.

Although we are exerting our best efforts to maintain the quality of these products, we cannot guarantee that they will never cause short circuiting and open circuitry. Therefore, when designing an equipment or device with which the priority is given to the safety, you will please carefully study the influences to the whole equipment of a single function failure of Potentiometers and Encoders in advance to make out a fail-safe design providing.

CLASS.NO.	TITLE
	SPECIFICATIONS
Feature	
This is a potentiometer with D.C. magnet motor and it is adjustable by both manual shaft and motor.	
Temperature for operating and storage	
1. Dimensions :	See attached drawing
2. Operating temperature :	-10 °C ~ +70 °C
3. Storage temperature :	-20 °C ~ +80 °C
4. Motor :	D.C. magnet motor (With 6V Disk Varistor)
Mechanical specifications	
1. Operation :	manual operation and motor drive
2. Total rotational angle :	300° ± 3°
3. Rotational speed :	12 ± 3 sec/300° (at 4.5V D.C. applied to motor)
4. Direction of rotation :	C.W. rotation at normal polarity. (When the potentiometer is looked at from the shaft side.)
5. Mechanical noise :	Continuous, monotonous, not unpleasant sound to be heard. To be mutually discussed when questionable.
6. Rotational torque :	15 ~ 45 mN·m (Rotational speed 60° /sec.)
7. Stopper strength of shaft	
with manual operation :	No damage with an application of 0.9 N·m.
with motor drive :	Shaft must be slipped at the both ends of manual rotation.
8. Bushing nut tightening strength :	
Tightening torque to be no greater than 1.5 N·m.	
(Pay attention otherwise the strength may not be assured.)	
9. Push / pull strength :	
No damages with an application of push or pull force	
100 N for 10 sec	
10. Resistance to soldering heat :	
After soldering there shall be no evidence of poor contact between resistance element and terminals, or any physical damage as a result of the test.	
The terminal of the potentiometer	
less than 350 °C and within 5 sec.	
The terminal of the motor	
less than 350 °C and within 2 sec.	




CLASS.NO.	TITLE										
	SPECIFICATIONS										
Electrical specifications (100kΩ)											
1. Total resistance : Nominal total resistance ± 20% (10kΩ ≤ R ≤ 2MΩ)											
2. Rated voltage : 30V A.C. This potentiometer is designed for A.C. voltage only.											
3. Resistance taper : See (HSB02)											
4. Maximum attenuation level at full C.C.W. (*C.W.) position :											
	<table border="1"> <thead> <tr> <th>Total resistance</th> <th>Attenuation level</th> </tr> </thead> <tbody> <tr> <td>R ≥ 100kΩ</td> <td>100 dB min.</td> </tr> <tr> <td>100kΩ > R ≥ 50kΩ</td> <td>90 dB min.</td> </tr> <tr> <td>50kΩ > R ≥ 10kΩ</td> <td>80 dB min.</td> </tr> </tbody> </table>	Total resistance	Attenuation level	R ≥ 100kΩ	100 dB min.	100kΩ > R ≥ 50kΩ	90 dB min.	50kΩ > R ≥ 10kΩ	80 dB min.		
Total resistance	Attenuation level										
R ≥ 100kΩ	100 dB min.										
100kΩ > R ≥ 50kΩ	90 dB min.										
50kΩ > R ≥ 10kΩ	80 dB min.										
5. Insertion loss at full C.W. (*C.C.W.) position : 0.1 dB max.											
6. Gang error :											
	<table border="1"> <thead> <tr> <th>Total resistance</th> <th>Gang error</th> </tr> </thead> <tbody> <tr> <td>R ≥ 100kΩ</td> <td>5 dB max. between -80 dB less than -70 dB 3 dB max. between -70 dB less than -60 dB 2 dB max. between -60 dB ~ 0 dB</td> </tr> <tr> <td>100kΩ > R ≥ 50kΩ</td> <td>3 dB max. between -70 dB less than -60 dB 2 dB max. between -60 dB ~ 0 dB</td> </tr> <tr> <td>50kΩ > R ≥ 20kΩ</td> <td>3 dB max. between -60 dB less than -50 dB 2 dB max. between -50 dB ~ 0 dB</td> </tr> <tr> <td>20kΩ > R ≥ 10kΩ</td> <td>3 dB max. between -60 dB less than -40 dB 2 dB max. between -40 dB ~ 0 dB</td> </tr> </tbody> </table>	Total resistance	Gang error	R ≥ 100kΩ	5 dB max. between -80 dB less than -70 dB 3 dB max. between -70 dB less than -60 dB 2 dB max. between -60 dB ~ 0 dB	100kΩ > R ≥ 50kΩ	3 dB max. between -70 dB less than -60 dB 2 dB max. between -60 dB ~ 0 dB	50kΩ > R ≥ 20kΩ	3 dB max. between -60 dB less than -50 dB 2 dB max. between -50 dB ~ 0 dB	20kΩ > R ≥ 10kΩ	3 dB max. between -60 dB less than -40 dB 2 dB max. between -40 dB ~ 0 dB
Total resistance	Gang error										
R ≥ 100kΩ	5 dB max. between -80 dB less than -70 dB 3 dB max. between -70 dB less than -60 dB 2 dB max. between -60 dB ~ 0 dB										
100kΩ > R ≥ 50kΩ	3 dB max. between -70 dB less than -60 dB 2 dB max. between -60 dB ~ 0 dB										
50kΩ > R ≥ 20kΩ	3 dB max. between -60 dB less than -50 dB 2 dB max. between -50 dB ~ 0 dB										
20kΩ > R ≥ 10kΩ	3 dB max. between -60 dB less than -40 dB 2 dB max. between -40 dB ~ 0 dB										
7. Sliding noise : Less than 47mV measured by JIS C 6443. (Neglected a impulsive noise at the C.W. and C.C.W. ends of position.)											
8. Insulation resistance											
Potentiometer section :	More than 100MΩ at 500V D.C.										
Motor section :	More than 1MΩ at 100V D.C.										
9. Withstand voltage											
Potentiometer section :	500V A.C. for 1 minute.										
10. Supply voltage of motor : 4 ~ 6V D.C.											
11. Motor current (at 4.5V D.C. applied to motor)											
Normal operation :	100mA max.										
Slipping operation											
at both ends :	150mA max.										
12. Rated voltage for motor : 4.5V D.C.											
Endurance specifications											
1. Rotational life : 15,000 cycles min.											
ALPS ELECTRIC CO., LTD.											
APPD.	CHKD.	DSGD.	TITLE								
Oct. 4 '99		Oct. 1 '99									
SYMB.		DOCUMENT NO.									
		5K272AMS-5									

18

10 R I



ALPS ELECTRIC CO., LTD
1-7 YUKIGAYA OTSUKA-CHO STA-KU TOKYO JAPAN



AT 150° C.W. SHAFT ROTATION FROM FULL C.C.W. POSITION, VOLTAGE PERCENT SHALL FALL WITHIN THE LIMITS OF 40 - 60 PERCENT.

Original	81-01-21	S.S.T.K.H.S	APPD.	UNIT	DOCUMENT NO.
SYMB	DATE	APPD	CHKD	DSGD	
					HSB02


DSGD: K. Chanon May. 11 '96
CHKD: S. Sasaki May. 13 '96

< はんだ付け時の注意事項 >

図のようにP. W. B.の上面に はんだ付けをする配線は、お避け下さい。


Caution for soldering





Please avoid soldering on upper surface of P. W. B. as shown



ALPS ELECTRIC CO., LTD.					
APPD	CHKD	DSGD	TITLE		
1-21	1-21	1-21			
96.1.11	96.1.11	96.1.11	DOCUMENT NO.		
吉岡	佐藤	大矢	4K-1		
SYMB	DATE	APPD	CHKD	DSGD	

CLASS.NO.	TITLE
	S P E C I F I C A T I O N S
<p>Note</p> <p>1.The standard test shall be subject to a temperature from 5 °C to 35 °C and relative humidity from 45% to 85%. Test shall be done under environmental requirements of a temperature of 20° ± 2 °C and relative humidity of 65 ± 5% if a decision is in question.</p> <p>2.Notice on motor</p> <p>1)Motor terminals shall not be bent more than twice.</p> <p>2)Soldering to the motor terminals shall be within a few second, not to cause the transformation of terminal base plastics. And, avoid that the flux flows into the motor. Pay special attention to the terminals when they are wave soldered.</p> <p>If the flux flows into the motor, it may cause a poor contact.</p> <p>3)Motor terminal should not be pressed inside the motor. It may cause a poor contact in the motor.</p> <p>4)Pay attention that a piece of iron and an alien substance are not crepted into the motor.</p> <p>5)In operation, temperature around the motor produce an effect on the performance and life. Pay special attention in high temperature and humidity. Storage in high temperature and humidity, and in corrosive gas, shall be avoided.</p> <p>6)In case, using the adhesive agent and the seal agent etc.for fit up, make sure that there is no generation of the harmful gas for motor.(including all chemicals around the motor.) Pay special attention to cyanogen system adhesive agent and organically system silicone.</p>	

CLASS.NO.	TITLE				
	S P E C I F I C A T I O N S				
<p>3.Power supply</p> <p>Regulated D.C. power supply shall be used. (ripple to be 1% max.)Motor terminal shall not be conected with fixed resistors in series.</p> <p>And supply current is to be 350mA min.</p> <p>4.Knob</p> <p>The material of the knob shall be insulation material. As potentiometer is not grounded, conductive material of the knob may cause a earth noise.</p> <p>5.The items except above mentioned items shall meet or exceed JIS C 6443.</p>					
 ALPS ELECTRIC CO., LTD.					
APPD.	CHKD.	DSGD.	TITLE		
Apr. 19 '90 S. Hironaka	Apr. 18 '90 R. Kusaka	Apr. 17 '90 S. Hironaka			
SYMB.	DATE	APPD.	CHKD.	DSGD.	DOCUMENT NO.
					4K16M-1



取付穴寸法図許容差±0.1
挿入側よりみた図
P. W. B. MOUNTING DETAIL
TOLERANCE 0.1
VIEWED FROM MOUNTING SIDE

指定なき部分の許容差 TOLERANCES UNLESS OTHERWISE SPEC	
$L \leq 10$	±0.3
$10 < L < 100$	±0.5
$100 \leq L$	±0.8
角度 ANGULAR DIMENSION	±5°

				モータ基板付	
PART NO.	NAME	MATERIAL NAME / CODE	FINISH		
ALPS ALPS ELECTRIC CO., LTD.					
DSGN. セツケ11-906011 Y. SAITOH 94-04-21			SCALE 1:1		
CHKD. <i>m. Saitoh</i> 94-04-22			UNIT mm	TITLE 27形1軸2連モーター-VR組立図	
APPD. <i>K. Yamazaki</i> 94-04-22				DOCUMENT NO. 1994. 5. 9 K272AMC02C	
SYMB	DATE	APPD	CHKD	DSGD	

89.3g OR