

Single phase, primary switched mode power supply **PC-0124-200-0**



Advantages

| |
|---|
| Stabilised and adjustable output voltage |
| Fast tripping of standard bi-metal circuit breakers |
| DC OK signal contact |
| Parallel operation |
| Push-In terminals |
| Robust DIN rail mounting |

Applications

Power Compact combines the basic functionality of an economic power supply with the essential features to maximize the availability of your system.

Standards

Primary switched mode power supply
to UL 60950, UL 508

Safety:
EN 61558-2-17, EN 60950 (SELV), EN 60204 (PELV)

EMC:
EN 61204-3

Approvals



Single phase, primary switched mode power supply

PC-0124-200-0

| Type | PC-0124-200-0 |
|--|---|
| Electrical data | |
| Input | |
| Input rated voltage | 100 - 240 Vac |
| Input voltage range | 85 - 264 Vac (120 - 372 Vdc) |
| Input voltage derating | -2.5 %/Vac < 100 Vac |
| Rated frequency range | 44 Hz - 66 Hz / 0 Hz |
| Input rated current (rated load) | 5.56 A (100 Vac) / 2.23 A (230 Vac) |
| Starting current limiter | < 30 A, NTC (active) |
| Switch-on time | 0.45 s (100 Vac) / 0.2 s (230 Vac) |
| Mains buffering | 20 ms (100 Vac) / 20 ms (230 Vac) |
| Power factor | 0.98 (active PFC) |
| Input fuse internal | 10 A |
| Recommended back-up fuse (circuit breaker) | 10 A, 16 A, characteristic B, C |
| Transient surge voltage protection | Varistor |
| Output | |
| Output rated voltage | 24 Vdc |
| Output voltage range | 23 - 28.5 Vdc |
| Output limited current | typ. 22 A (contant current) |
| Tripping of LS circuit breakers | max. B6, C6, K4 |
| Parallel connection | Yes |
| Serial operation | Yes |
| Power dissipation, no load/rated load | 7.2 / 42.4 W (230 Vac) |
| Max. power losses | 68.3 W (100 Vac / 24 V / 20 A) |
| Ripple factor | typ. 70 mVss |
| Efficiency | typ. 92 % |
| Resistance to reverse feed max. | 35 Vdc |
| Over-voltage-protection | max. 40 Vdc |
| Output rated current | 20 A |
| Signaling | |
| Status display | LED green |
| Signal output | Relay contact |
| Environment | |
| Cooling method | natural convection |
| Ambient temperature | -25°C ... +70°C |
| Storage temperature | -25°C ... +85°C |
| Derating | -5 %/K > +60°C @ 196 - 264 Vac -2.5 %/K > +50°C @ 85 - 195 Vac |
| Required minimum spacing (left/right) | - |
| Required minimum spacing (over/under) | 50 mm |
| Safety and protection | |
| Protection index | IP 20 |
| Safety class | I, with PE connection |
| Order numbers | |
| Order Number | PC-0124-200-0 |

| Type | PC-0124-200-0 |
|-----------------------------|---|
| Mechanical data | |
| Input | |
| Terminals Input | Push-In Terminals, max 2.5 mm ² |
| Output | |
| Terminals Output | Push-In Terminals, max 6 mm ² |
| Signaling | |
| Terminals signaling | Push-In Terminals, max 2.5 mm ² |
| Environment | |
| Mounting position | horizontal for standard rail DIN TH 35 |
| Measures and weights | |
| Weight | 1.60 kg |
| Dimensions W x H x D | 95 x 127 x 159 mm |