

Specification Sheet

Product	Inspect item	Inspect standard	Defect grade	Remark		
Velcro (KL10X3000C)	1. Appearance Veil: 0.22 Filling:1400 Cotton yarn: 1400	1. Take an ordinary gel first and laminated with hook and loop, 2. For white product, Pollution prone 3. Inspection method: Hook and Loop sticky together with good lateral tensile strength 4. Others appearance requirement: same as normal Velcro.	MA MA/MI			
	2. Size	1. Length: 25M (25.15~25.25M) 2. Width: width < 50,mm, tolerance ± 1mm 50mm ≤ width ≤ 110mm, tolerance ± 2mm width ≥ 110mm, tolerance ± (2~3)mm	MA			
	3. Test the strength of tension 0.90EC/sq.cm 230g/sq.cm	Tension	Width (mm)	Lateral tension(kg)	Peel strength	Reducing rate
			10	6.0 (above)	2000 (times)	10%(under)
			16	6.0 (above)	2000 (times)	10%(under)
			20	7.0 (above)		
			25	10.0 (above)	5000 (times)	15%(under)
			38	15.0 (above)		
			50	19.0 (above)	10000 (times)	25%(under)
		100	46.0 (above)			
Tired		Number of times used	Lateral tension(kg)	Peel strength		
		1000	90%	90%	MA	
	2000	70%	70%			
	5000	60%	60%			
Others				MA		
4. Packing	25M/Roll, or catch customer's request		MA/MI			
5. Environmental	SGS standard, RoHs, ITTC certificate		MA			