

Surface Mount Type

Series: **FC** Type: **V**



■ Features

- Endurance : 105 °C 1000 h
- Low impedance (1/2 for HA series)
- Vibration-proof product is available upon request. ($\phi 8 \leq$)
- RoHS directive compliant


■ Specifications

Category Temp. Range	-40 °C to +105 °C							
Rated W.V. Range	6.3 V.DC to 50 V.DC							
Nominal Cap. Range	1 µF to 1500 µF							
Capacitance Tolerance	±20 % (120 Hz/+20 °C)							
DC Leakage Current	I ≤ 0.01 CV or 3 (µA) After 2 minutes (Whichever is greater)							
tan δ	Please see the attached standard products list							
Characteristics at Low Temperature	W.V. (V)	6.3	10	16	25	35	50	(Impedance ratio at 120 Hz)
	Z(-25 °C) / Z(+20 °C)	2	2	2	2	2	2	
	Z(-40 °C) / Z(+20 °C)	3	3	3	3	3	3	
Endurance	After applying rated working voltage for 1000 hours at +105 °C±2 °C and then being stabilized at +20 °C, Capacitors shall meet the following limits.							
	Capacitance change	±20 % of initial measured value						
	tan δ	≤ 200 % of initial specified value						
	DC leakage current	≤ initial specified value						
Shelf Life	After storage for 1000 hours at +105 °C±2 °C with no voltage applied and then being stabilized at +20 °C, capacitors shall meet the limits specified in Endurance.(With voltage treatment)							
Resistance to Soldering Heat	After reflow soldering and then being stabilized at +20 °C, capacitor shall meet the following limits.							
	Capacitance change	±10 % of initial measured value						
	tan δ	≤ initial specified value						
	DC leakage current	≤ initial specified value						

■ Marking

Example: 6.3 V 22 μ F


Marking color : BLACK



Rated Voltage Mark

j	6.3 V
A	10 V
C	16 V
E	25 V
V	35 V
H	50 V

■ Dimensions in mm (not to scale)



Size code	D	L	A, B	H max.	I	W	P	K
B	4.0	5.4	4.3	5.5	1.8	0.65 ± 0.1	1.0	0.35-0.20 to +0.15
C	5.0	5.4	5.3	6.5	2.2	0.65 ± 0.1	1.5	0.35-0.20 to +0.15
D	6.3	5.4	6.6	7.8	2.6	0.65 ± 0.1	1.8	0.35-0.20 to +0.15
E*	8.0	6.2	8.3	9.5	3.4	0.65 ± 0.1	2.2	0.35-0.20 to +0.15
F*	8.0	10.2	8.3	10.0	3.4	0.90 ± 0.2	3.1	0.70 ± 0.2
G*	10.0	10.2	10.3	12.0	3.5	0.90 ± 0.2	4.6	0.70 ± 0.2

Standard Products

Endurance : 105 °C 1000 h

W.V.	Cap. (±20 %)	Case size			Specification			Part No. (RoHS:compliant)	Reflow	Min. Packaging Q'ty
		Dia.	Length	Size Code	Ripple Current (100 kHz) (+105°C) (mA r.m.s.)	$\tan \delta$ (120 Hz) (+20 °C)	Impedance (100 kHz) (+20 °C) (Ω)			Taping
(V)	(μ F)	(mm)	(mm)							(pcs)
6.3	22	4	5.4	B	60	0.26	3.00	EEEF0J220R	(1)	2000
	47	5	5.4	C	95	0.26	1.80	EEEF0J470R	(1)	1000
	68	6.3	5.4	D	140	0.26	1.00	EEEF0J680P	(1)	1000
	100	6.3	5.4	D	140	0.26	1.00	EEEF0J101P	(1)	1000
	220	8	6.2	E	230	0.26	0.40	EEEF0J221P	(2)	1000
	330	8	10.2	F	450	0.26	0.30	EEEF0J331P	(2)	500
	1000	10	10.2	G	670	0.26	0.15	EEEF0J102P	(2)	500
	1500	10	10.2	G	670	0.26	0.15	EEEF0J152P	(2)	500
10	33	5	5.4	C	95	0.19	1.80	EEEF0A330R	(1)	1000
	100	8	6.2	E	230	0.19	0.40	EEEF0A101P	(2)	1000
	150	8	6.2	E	230	0.19	0.40	EEEF0A151P	(2)	1000
	220	8	10.2	F	450	0.19	0.30	EEEF0A221P	(2)	500
	470	10	10.2	G	670	0.19	0.15	EEEF0A471P	(2)	500
	1000	10	10.2	G	670	0.19	0.15	EEEF0A102P	(2)	500
16	10	4	5.4	B	60	0.16	3.00	EEEF0C100R	(1)	2000
	22	5	5.4	C	95	0.16	1.80	EEEF0C220R	(1)	1000
	47	6.3	5.4	D	140	0.16	1.00	EEEF0C470P	(1)	1000
	68	8	6.2	E	230	0.16	0.40	EEEF0C680P	(2)	1000
	100	8	6.2	E	230	0.16	0.40	EEEF0C101P	(2)	1000
	220	10	10.2	G	670	0.16	0.15	EEEF0C221P	(2)	500
	330	10	10.2	G	670	0.16	0.15	EEEF0C331P	(2)	500
	470	10	10.2	G	670	0.16	0.15	EEEF0C471P	(2)	500
	680	10	10.2	G	670	0.16	0.15	EEEF0C681P	(2)	500
25	6.8	4	5.4	B	60	0.14	3.00	EEEF0E68R8	(1)	2000
	22	6.3	5.4	D	140	0.14	1.00	EEEF0E220P	(1)	1000
	33	6.3	5.4	D	140	0.14	1.00	EEEF0E330P	(1)	1000
	47	8	6.2	E	230	0.14	0.40	EEEF0E470P	(2)	1000
	68	8	10.2	F	450	0.14	0.30	EEEF0E680P	(2)	500
	100	8	10.2	F	450	0.14	0.30	EEEF0E101P	(2)	500
	220	10	10.2	G	670	0.14	0.15	EEEF0E221P	(2)	500
	330	10	10.2	G	670	0.14	0.15	EEEF0E331P	(2)	500
35	470	10	10.2	G	670	0.14	0.15	EEEF0E471P	(2)	500
	1	4	5.4	B	60	0.12	3.00	EEEF0V1R0R	(1)	2000
	2.2	4	5.4	B	60	0.12	3.00	EEEF0V2R2R	(1)	2000
	3.3	4	5.4	B	60	0.12	3.00	EEEF0V3R3R	(1)	2000
	4.7	4	5.4	B	60	0.12	3.00	EEEF0V4R7R	(1)	2000
	6.8	5	5.4	C	95	0.12	1.80	EEEF0V6R8R	(1)	1000
	10	5	5.4	C	95	0.12	1.80	EEEF0V100R	(1)	1000
	22	6.3	5.4	D	140	0.12	1.00	EEEF0V220P	(1)	1000
	33	8	6.2	E	230	0.12	0.40	EEEF0V330P	(2)	1000
	47	8	6.2	E	230	0.12	0.40	EEEF0V470P	(2)	1000
	100	10	10.2	G	670	0.12	0.15	EEEF0V101P	(2)	500
50	220	10	10.2	G	670	0.12	0.15	EEEF0V221P	(2)	500
	330	10	10.2	G	670	0.12	0.15	EEEF0V331P	(2)	500
	1	4	5.4	B	30	0.12	5.00	EEEF0H1R0R	(1)	2000
	2.2	4	5.4	B	30	0.12	5.00	EEEF0H2R2R	(1)	2000
	3.3	4	5.4	B	30	0.12	5.00	EEEF0H3R3R	(1)	2000
	4.7	5	5.4	C	50	0.12	3.00	EEEF0H4R7R	(1)	1000
	10	6.3	5.4	D	70	0.12	2.00	EEEF0H100P	(1)	1000
	22	8	6.2	E	120	0.12	0.70	EEEF0H220P	(2)	1000
	33	8	10.2	F	300	0.12	0.60	EEEF0H330P	(2)	500
	47	10	10.2	G	500	0.12	0.30	EEEF0H470P	(2)	500
	100	10	10.2	G	500	0.12	0.30	EEEF0H101P	(2)	500
	220	10	10.2	G	500	0.12	0.30	EEEF0H221P	(2)	500

The taping dimensions are explained on p.177 of our Catalog.

Please use it as a reference guide.

Reflow Profile (Fig-1 to Fig-11) listed on p.175 of our Catalog.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.