



Metal Film Leaded Precision Resistor – MFR Series

Construction



①	Insulation Coating (Expose Resin)	⑤	Resistor Layer (Nickel alloy)
②	Trimming Line	⑥	Marking (Expose)
③	Ceramic Core (Alumina ceramic)	⑦	Lead Wire (Tinned annealed copper wire)
④	Electrode Cap (Tinned iron cap)		

Features

- Excellent overall stability
- Very tight tolerance down to $\pm 0.05\%$
- Extremely low TCR down to $\pm 5 \text{ PPM}/^\circ\text{C}$
- High power rating up to 3 Watts
- Excellent ohmic contact

Applications


- Automotive
- Telecommunication
- Medical Equipment

Dimensions

Unit: mm

Type	L	D	H	d	Weight (g) (1000pcs)
MFR0318	3.3+0.7/-0.2	1.8±0.3	29±2.0	0.45±0.03	90
MFR0623	6.3±0.5	2.3±0.3	28±2.0	0.55±0.03	150
MFR0723	6.8±0.4	2.35±0.3	26±3.0	0.6±0.05	190
MFR0932	9.0±0.5	3.2±0.5	26±2.0	0.65±0.03	350
MFR1035	10.0±0.4	3.5±0.3	25±3.0	0.6±0.05	348
MSW0414 => MFR1145	11.5±1.0	4.5±0.5	35±2.0	0.78±0.03	770
MFR1550	15.5±1.0	5.0±0.5	32±2.0	0.78±0.03	1040

Derating Curve



Part Numbering

MFR	0318	B	T	N	W	1001	MA
Product Type	Dimensions (L×D)	Resistance Tolerance	Packaging Code	TCR (PPM/°C)	Power Rating	Resistance	Special
	0318: 3.3x1.8 0623: 6.3x2.3 0723: 6.8x2.35 0932: 9.0x3.2 1035: 10.0x3.5 1145: 11.5x4.5 1550: 15.5x5.0	A: $\pm 0.05\%$ B: $\pm 0.1\%$ C: $\pm 0.25\%$ D: $\pm 0.5\%$ F: $\pm 1\%$	A: Ammo B: Bulk T: Taping Reel	S: ± 5 B: ± 10 N: ± 15 C: ± 25 D: ± 50 E: ± 100	: Standard R: 3W S: 2W T: 1W U: 1/2W V: 1/4W	R100: 0.1Ω 0010: 1Ω 1000: 100Ω 2201: 2200Ω 1001: 1KΩ 1004: 1MΩ	: Standard MA: MA-type MB: MB-type MC: MC-type FA: FA-type FB: FB-type FC: FC-type PA: PA-type PB: PB-type PC: PC-type

Electrical Characteristics

Standard Electrical Specifications

Item Type	Power Rating at 70°C	Operating Temp. Range	Max. Operating Voltage	Max. Overload Voltage	Dielectric Withstanding Voltage	Resistance Range			Resistance Range		TCR (PPM/°C)
						±0.05%	±0.1%	±0.25%	±0.5%	±1%	
0318	1/8W	-55 ~ +155°C	200V	400V	300V	100Ω 100KΩ			10Ω 1MΩ	±15 ±25 ±50 ±100	
0623	1/4W		250V	500V	500V						
0932	1/2W		350V	700V	500V						
1145	1W		450V	1000V	1000V						
1550	2W		500V	1000V	1000V						

High Power Rating Electrical Specifications

Item Type	Power Rating at 70°C	Operating Temp. Range	Max. Operating Voltage	Max. Overload Voltage	Dielectric Withstanding Voltage	Resistance Range			Resistance Range		TCR (PPM/°C)
						±0.05%	±0.1%	±0.25%	±0.5%	±1%	
0318	1/4W	-55 ~ +155°C	200V	400V	400V	100Ω 100KΩ			10Ω 1MΩ	±15 ±25 ±50 ±100	
0623	1/2W		300V	600V	500V						
0932	1W		400V	800V	700V						
1145	2W		500V	1000V	1000V						
1550	3W		500V	1000V	1000V						

Electrical Characteristics of Low TCR Series

Standard Electrical Specifications

Item Type	Power Rating at 70°C	Operating Temp. Range	Max. Operating Voltage	Max. Overload Voltage	Dielectric Withstanding Voltage	Resistance Range		TCR (PPM/°C)
						±0.05%	±0.1%	
0723	1/4W	-55 ~ +155°C	250V	500V	250V	10Ω 1MΩ		±5 ±10 ±15 ±25
1035	1/2W		300V	600V	300V			

High Power Rating Electrical Specifications

Item Type	Power Rating at 70°C	Operating Temp. Range	Max. Operating Voltage	Max. Overload Voltage	Dielectric Withstanding Voltage	Resistance Range		TCR (PPM/°C)
						±0.05%	±0.1%	
0723	1/2W	-55 ~ +155°C	300V	600V	300V	10Ω 1MΩ		±5 ±10 ±15 ±25
1035	1W		350V	700V	500V			

Environmental Characteristics

Item	Requirement	Test Method
Short Time Overload	±0.25%	RCWV*2.5 or Max. overload voltage for 5 seconds
Insulation Resistance	> 1000MΩ	Apply 100V _{DC} for 1 minute
Endurance	±0.2%	70±2°C, Max. working voltage for 1000 hrs with 1.5 hrs "ON" and 0.5 hrs "OFF"
Damp Heat with Load	±0.3%	40±2°C, 90~95% R.H. Max. working voltage for 1000 hrs with 1.5 hrs "ON" and 0.5 hrs "OFF"
Solderability	90% min. Coverage	245±5°C for 3 seconds
Dielectric Withstanding Voltage	By Type	Apply Max. Overload Voltage for 1 minute
Temperature Coefficient	By Type	Resistance value at room temperature and room Temperature+100°C
Pulse Overload	±0.75%	4 times RCWV for 10000 cycles with 1sec "ON" and 25 sec "OFF"
Resistance To Solvent	No deterioration of coatings and markings	Trichroethane for 1 min. with ultrasonic
Terminal Strength	Tensile: ≥ 2.5kg	Direct Load for 10 sec. In the direction off the terminal leads
Shelf life	ΔR=±0.1%	12 months at room temperature 25±3°C, 80%RH Max.

■ Reference Standards: MIL-STD-202, JIS-C 5201-1

■ Storage Temperature: 25±3°C; Humidity < 80%RH