

YAGEO

**Product Selection Tables
2005**

MLCC

Yageo brand



YAGEO



Table of Contents

| Table of contents | |
|--|----|
| MLCC - NP0 / Yageo brand | 2 |
| NP0, 16V, general purpose | 2 |
| NP0, 25V, general purpose | 3 |
| NP0, 50V, general purpose | 4 |
| NP0, 100V, general purpose | 6 |
| NP0, 200V and 500V, medium voltage | 7 |
| MLCC - X7R / Yageo brand | 8 |
| X7R, 10V, general purpose | 8 |
| X7R, 16V and 25V, general purpose | 9 |
| X7R, 50V and 100V, general purpose | 10 |
| X7R, 200V, 250V and 500V, medium voltage | 11 |
| MLCC - Y5V / Yageo brand | 12 |
| Y5V, 10V to 50V, general purpose | 12 |
| General information | 13 |
| Ordering and packing | 13 |
| Yageo - A Global Company | 15 |
| Contact information | 15 |

MLCC - NP0 / Yageo brand

NP0, 16V, general purpose

| NP0 - 16V | | | |
|-----------------|------------------------------------|-----------|-----------|
| General purpose | | | |
| Capacitance | Last 3 digits of Yageo part number | 16V | |
| | | 0402 | 0603 |
| 270 pF | 271 | 0.5 ±0.05 | |
| 330 pF | 331 | | |
| 390 pF | 391 | | |
| 470 pF | 471 | | |
| 1.8 nF | 182 | | 0.8 ±0.07 |
| 2.2 nF | 222 | | |
| 2.7 nF | 272 | | |
| 3.3 nF | 332 | | |
| Tape width | | 8mm | |

Note: Values in shaded cells indicate thickness class (Unit: mm)

MLCC - NP0 / Yageo brand

NP0, 25V, general purpose

| NP0 - 25V | | | | | |
|-----------------|------------------------------------|-----------|-----------|-----------|------------|
| General purpose | | | | | |
| Capacitance | Last 3 digits of Yageo part number | 25V | | | |
| | | 0603 | 0805 | 1206 | 1210 |
| 820 pF | 821 | 0.8 ±0.07 | | | |
| 1000 pF | 102 | | | | |
| 1.2 nF | 122 | | | | |
| 1.5 nF | 152 | | | | |
| 3.3 nF | 332 | | 0.85 ±0.1 | | |
| 3.9 nF | 392 | | 1.25 ±0.1 | | |
| 4.7 nF | 472 | | | | |
| 8.2 nF | 822 | | | 0.85 ±0.1 | |
| 10 nF | 103 | | | | |
| 12 nF | 123 | | | | 0.6 ±0.1 |
| 15 nF | 153 | | | | 0.85 ±0.1 |
| 18 nF | 183 | | | | |
| 22 nF | 223 | | | | 1.15 ±0.15 |
| Tape width | | 8mm | | | |

Note: Values in shaded cells indicate thickness class (Unit: mm)

MLCC - NP0 / Yageo brand

NP0, 50V, general purpose

| NP0 - 50V | | | | | | | |
|-----------------|------------------------------------|-----------|-----------|-----------|-----------|-----------|----------|
| General purpose | | | | | | | |
| Capacitance | Last 3 digits of Yageo part number | 50V | | | | | |
| | | 0402 | 0603 | 0805 | 1206 | 1210 | 1812 |
| 0.47 pF | R47 | 0.5 ±0.05 | 0.8 ±0.07 | 0.6 ±0.1 | 0.6 ±0.1 | | |
| 0.56 pF | R56 | | | | | | |
| 0.68 pF | R68 | | | | | | |
| 0.82 pF | R82 | | | | | | |
| 1 pF | 1R0 | | | | | | |
| 1.2 pF | 1R2 | | | | | | |
| 1.5 pF | 1R5 | | | | | | |
| 1.8 pF | 1R8 | | | | | | |
| 2.2 pF | 2R2 | | | | | | |
| 2.7 pF | 2R7 | | | | | | |
| 3.3 pF | 3R3 | | | | | | |
| 3.9 pF | 3R9 | | | | | | |
| 4.7 pF | 4R7 | | | | | | |
| 5.6 pF | 5R6 | | | | | | |
| 6.8 pF | 6R8 | | | | | | |
| 8.2 pF | 8R2 | | | | | | |
| 10 pF | 100 | | | | | | |
| 12 pF | 120 | | | | | | |
| 15 pF | 150 | | | | | | |
| 18 pF | 180 | | | | | | |
| 22 pF | 220 | | | | | | |
| 27 pF | 270 | | | | | | |
| 33 pF | 330 | | | | | | |
| 39 pF | 390 | | | | | | |
| 47 pF | 470 | | | | | 0.6 ±0.1 | |
| 56 pF | 560 | | | | | | |
| 68 pF | 680 | | | | | | |
| 82 pF | 820 | | | | | | |
| 100 pF | 101 | | | | | | |
| 120 pF | 121 | | | | | | |
| 150 pF | 151 | | | | | | |
| 180 pF | 181 | | | | | | |
| 220 pF | 221 | | | | | | |
| 270 pF | 271 | | | | | | |
| 330 pF | 331 | | | | | | 0.6 ±0.1 |
| 390 pF | 391 | | | | | | |
| 470 pF | 471 | | | | | | |
| 560 pF | 561 | | | | | | |
| 680 pF | 681 | | | | | | |
| 820 pF | 821 | | | | | | |
| 1000 pF | 102 | | | | | | |
| 1.2 nF | 122 | | | 0.85 ±0.1 | | | |
| 1.5 nF | 152 | | | | | | |
| 1.8 nF | 182 | | | | | | |
| 2.2 nF | 222 | | | 1.25 ±0.1 | | | |
| 2.7 nF | 272 | | | | | | |
| 3.3 nF | 332 | | | | 0.85 ±0.1 | | |
| 3.9 nF | 392 | | | | | | |
| 4.7 nF | 472 | | | | | | |
| 5.6 nF | 562 | | | | 1.15 ±0.1 | 0.85 ±0.1 | |
| 6.8 nF | 682 | | | | | | |

MLCC - NP0 / Yageo brand

NP0, 50V, general purpose

| NP0 - 50V | | | | | | | | |
|-----------------|------------------------------------|------|------|------|------|------|------------|--|
| General purpose | | | | | | | | |
| Capacitance | Last 3 digits of Yageo part number | 50V | | | | | | |
| | | 0402 | 0603 | 0805 | 1206 | 1210 | 1812 | |
| 8.2 nF | 822 | | | | | | | |
| 10 nF | 103 | | | | | | | |
| 12 nF | 123 | | | | | | 0.85 ±0.1 | |
| 15 nF | 153 | | | | | | | |
| 18 nF | 183 | | | | | | 1.15 ±0.15 | |
| 22 nF | 223 | | | | | | | |
| Tape width | | 8mm | | | | | 12mm | |

Note: Values in shaded cells indicate thickness class (Unit: mm)

MLCC - NP0 / Yageo brand

NP0, 100V, general purpose

| NP0 - 100V | | | | | | |
|-----------------|------------------------------------|-----------|-----------|-----------|-----------|------------|
| General purpose | | | | | | |
| Capacitance | Last 3 digits of Yageo part number | 100V | | | | |
| | | 0603 | 0805 | 1206 | 1210 | 1812 |
| 10 pF | 100 | 0.8 ±0.07 | 0.6 ±0.1 | 0.6 ±0.1 | | |
| 12 pF | 120 | | | | | |
| 15 pF | 150 | | | | | |
| 18 pF | 180 | | | | | |
| 22 pF | 220 | | | | | |
| 27 pF | 270 | | | | | |
| 33 pF | 330 | | | | | |
| 39 pF | 390 | | | | | |
| 47 pF | 470 | | | | | |
| 56 pF | 560 | | | | | |
| 68 pF | 680 | | | | | |
| 82 pF | 820 | | | | | |
| 100 pF | 101 | | | | | |
| 120 pF | 121 | | | | | |
| 150 pF | 151 | | | | | |
| 180 pF | 181 | | | | | |
| 220 pF | 221 | | | | | |
| 270 pF | 271 | | | | | |
| 330 pF | 331 | | | | | |
| 390 pF | 391 | | | | | |
| 470 pF | 471 | | | | | |
| 560 pF | 561 | | | | | |
| 680 pF | 681 | | | | | |
| 820 pF | 821 | | | | | |
| 1000 pF | 102 | | | | | |
| 1.2 nF | 122 | | 0.85 ±0.1 | | | |
| 1.5 nF | 152 | | | | | |
| 1.8 nF | 182 | | | | | |
| 2.2 nF | 222 | | 1.25 ±0.1 | | | |
| 2.7 nF | 272 | | | | | |
| 3.3 nF | 332 | | | 0.85 ±0.1 | | |
| 3.9 nF | 392 | | | | | |
| 4.7 nF | 472 | | | | | |
| 5.6 nF | 562 | | | 1.15 ±0.1 | | |
| 6.8 nF | 682 | | | | | |
| 8.2 nF | 822 | | | | 0.85 ±0.1 | |
| 10 nF | 103 | | | | | |
| 12 nF | 123 | | | | | 0.85 ±0.1 |
| 15 nF | 153 | | | | | |
| 18 nF | 183 | | | | | 1.15 ±0.15 |
| 22 nF | 223 | | | | | |
| Tape width | | 8mm | | | | 12mm |

Note: Values in shaded cells indicate thickness class (Unit: mm)

MLCC - NP0 / Yageo brand

NP0, 200V and 500V, medium voltage

| NP0 - 200V and 500V | | | | | | | | | |
|---------------------|------------------------------------|-----------|-----------|------------|------------|-----------|------------|------------|------|
| Medium voltage | | | | | | | | | |
| Capacitance | Last 3 digits of Yageo part number | 200V | | | | 500V | | | |
| | | 0805 | 1206 | 1210 | 1812 | 1206 | 1210 | 1812 | |
| 10 pF | 100 | 0.6 ±0.1 | 0.6 ±0.1 | | | 0.6 ±0.1 | | | |
| 12 pF | 120 | | | | | | | | |
| 15 pF | 150 | | | | | | | | |
| 18 pF | 180 | | | | | | | | |
| 22 pF | 220 | | | | | | | | |
| 27 pF | 270 | | | | | | | | |
| 33 pF | 330 | | | | | | | | |
| 39 pF | 390 | | | | | | | | |
| 47 pF | 470 | | | | | | 0.85 ±0.1 | | |
| 56 pF | 560 | | | | | | | | |
| 68 pF | 680 | | | | | | | | |
| 82 pF | 820 | | | | | | | | |
| 100 pF | 101 | | | | | | | | |
| 120 pF | 121 | | | | | | | | |
| 150 pF | 151 | | | | | | | | |
| 180 pF | 181 | | | | | | | | |
| 220 pF | 221 | 0.85 ±0.1 | 0.85 ±0.1 | | | 0.85 ±0.1 | | | |
| 270 pF | 271 | | | | | | | | |
| 330 pF | 331 | | | | | | | | |
| 390 pF | 391 | | | | | | | | |
| 470 pF | 471 | | | | | | | | |
| 560 pF | 561 | 1.25 ±0.1 | | | | 1.15 ±0.1 | | | |
| 680 pF | 681 | | | | | | | | |
| 820 pF | 821 | | | | | | | | |
| 1000 pF | 102 | | | | | | 1.15 ±0.15 | | |
| 1.2 nF | 122 | | | | | | | | |
| 1.5 nF | 152 | | 1.15 ±0.1 | | | | | | |
| 1.8 nF | 182 | | | 0.85 ±0.1 | | | | | |
| 2.2 nF | 222 | | | | | | | 1.15 ±0.15 | |
| 2.7 nF | 272 | | | 1.15 ±0.15 | | | | | |
| 3.3 nF | 332 | | | | | | | | |
| 3.9 nF | 392 | | | | 0.85 ±0.1 | | | | |
| 4.7 nF | 472 | | | | 1.15 ±0.15 | | | | |
| 5.6 nF | 562 | | | | | | | | |
| Tape width | | 8mm | | | 12mm | | 8mm | | 12mm |

Note: Values in shaded cells indicate thickness class (Unit: mm)

MLCC - X7R / Yageo brand

X7R, 10V, general purpose

| X7R - 10V | | | | |
|-----------------|------------------------------------|-----------|-----------|-----------|
| General purpose | | | | |
| Capacitance | Last 3 digits of Yageo part number | 10V | | |
| | | 0603 | 0805 | 1206 |
| 150 nF | 154 | 0.8 ±0.07 | | |
| 220 nF | 224 | | 0.6 ±0.1 | |
| 330 nF | 334 | | 0.85 ±0.1 | |
| 470 nF | 474 | | | |
| 680 nF | 684 | | 1.25 ±0.1 | |
| 1000 nF | 105 | | | 0.85 ±0.1 |
| 1.5 µF | 155 | | | 1.15 ±0.1 |
| 2.2 µF | 225 | | | |
| 4.7 µF | 475 | | | 1.6 ±0.2 |
| Tape width | | 8 mm | | |

Note: Values in shaded cells indicate thickness class (Unit: mm)

MLCC - X7R / Yageo brand

X7R, 16V and 25V, general purpose

| X7R - 16V and 25V | | | | | | | | | | |
|-------------------|------------------------------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|
| General purpose | | | | | | | | | | |
| Capacitance | Last 3 digits of Yageo part number | 16V | | | | 25V | | | | |
| | | 0402 | 0603 | 0805 | 1206 | 0402 | 0603 | 0805 | 1206 | 1210 |
| 3.3 nF | 332 | | | | | 0.5 ±0.05 | | | | |
| 4.7 nF | 472 | | | | | | | | | |
| 6.8 nF | 682 | 0.5 ±0.05 | | | | | | | | |
| 10 nF | 103 | | | | | | 0.8 ±0.07 | 0.6 ±0.1 | | |
| 15 nF | 153 | | | | | | | | | |
| 22 nF | 223 | | | | | | | | | |
| 33 nF | 333 | | 0.8 ±0.07 | | | | | | | |
| 47 nF | 473 | 0.5 ±0.05 | | 0.6 ±0.1 | | | | 0.85 ±0.1 | | |
| 68 nF | 683 | | | | | | | | | |
| 100 nF | 104 | | | 0.85 ±0.1 | | | | | 0.85 ±0.1 | |
| 150 nF | 154 | | | | | | | | | |
| 220 nF | 224 | | | | 0.85 ±0.1 | | | | | 0.85 ±0.1 |
| 330 nF | 334 | | | 1.25 ±0.1 | | | | | 1.15 ±0.1 | |
| 470 nF | 474 | | | | 1.15 ±0.1 | | | | | |
| 680 nF | 684 | | | | | | | | | |
| 1000 nF | 105 | | | | | | | | 1.6 ±0.2 | |
| Tape width | | 8mm | | | | | | | | |

Note: Values in shaded cells indicate thickness class (Unit: mm)

MLCC - X7R / Yageo brand

X7R, 50V and 100V, general purpose

| X7R - 50V and 100V | | | | | | | | | | | | |
|--------------------|------------------------------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|------|
| General purpose | | | | | | | | | | | | |
| Capacitance | Last 3 digits of Yageo part number | 50V | | | | | | 100V | | | | |
| | | 0402 | 0603 | 0805 | 1206 | 1210 | 1812 | 0805 | 1206 | 1210 | 1812 | |
| 100 pF | 101 | 0.5 ±0.05 | 0.8 ±0.07 | | | | | | | | | |
| 150 pF | 151 | | | | | | | | | | | |
| 220 pF | 221 | | | 0.6 ±0.1 | 0.85 ±0.1 | | | 0.6 ±0.1 | 0.85 ±0.1 | | | |
| 330 pF | 331 | | | | | | | | | | | |
| 470 pF | 471 | | | | | | | | | | | |
| 680 pF | 681 | | | | | | | | | | | |
| 1000 pF | 102 | | | | | | | | | | | |
| 1.5 nF | 152 | | | | | | | | | | | |
| 2.2 nF | 222 | | | | | | | | | | | |
| 3.3 nF | 332 | | | | | | | | | | | |
| 4.7 nF | 472 | | | | | | | | | | | |
| 6.8 nF | 682 | | | | | | | | | | | |
| 10 nF | 103 | | | | | 0.85 ±0.1 | | | | | | |
| 15 nF | 153 | | | | | | | 0.85 ±0.1 | | | | |
| 22 nF | 223 | | | | | | | | | | | |
| 33 nF | 333 | | | 0.85 ±0.1 | | | | | | | | |
| 47 nF | 473 | | | | | | | | | 0.85 ±0.1 | | |
| 68 nF | 683 | | | | | | | | 1.15 ±0.1 | | | |
| 100 nF | 104 | | | | | | 1.15 ±0.1 | | | | 1.15 ±0.1 | |
| 150 nF | 154 | | | | 1.15 ±0.1 | 1.15 ±0.1 | | | | 1.15 ±0.1 | | |
| 220 nF | 224 | | | | | | | | | | | |
| 330 nF | 334 | | | | | | | | | | | |
| 470 nF | 474 | | | | | | | | | | 1.6 ±0.2 | |
| 680 nF | 684 | | | | | | | 1.6 ±0.2 | | | | |
| 1000 nF | 105 | | | | | | | | | | | |
| Tape width | | 8mm | | | | | 12mm | | 8mm | | | 12mm |

Note: Values in shaded cells indicate thickness class (Unit: mm)

MLCC - X7R / Yageo brand

X7R, 200V, 250V and 500V, medium voltage

| X7R - 200 V and 500 V | | | | | | | | |
|-----------------------|------------------------------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|
| Medium voltage | | | | | | | | |
| Capacitance | Last 3 digits of Yageo part number | 200V | | | | 500V | | |
| | | 0805 | 1206 | 1210 | 1812 | 1206 | 1210 | 1812 |
| 220 pF | 221 | 0.85 ±0.1 | | | | | | |
| 330 pF | 331 | | | | | | | |
| 470 pF | 471 | | | | | 1.15 ±0.1 | | |
| 680 pF | 681 | | 0.85 ±0.1 | | | | | |
| 1000 pF | 102 | | | | | | | |
| 1.5 nF | 152 | | | | | | | |
| 2.2 nF | 222 | | | | | | | |
| 3.3 nF | 332 | | | | | | 1.15 ±0.1 | |
| 4.7 nF | 472 | | | | | | | |
| 6.8 nF | 682 | 1.25 ±0.1 | | | | | | |
| 10 nF | 103 | | | | | | | 1.15 ±0.1 |
| 15 nF | 153 | | | | | | | |
| 22 nF | 223 | | 1.15 ±0.1 | 1.15 ±0.1 | | | | |
| 33 nF | 333 | | | | | | | |
| 47 nF | 473 | | | | 1.15 ±0.1 | | | |
| 68 nF | 683 | | | | | | | |
| 100 nF | 104 | | | | | | | |
| Tape width | | 8mm | | | 12mm | 8mm | | 12mm |

Note: Values in shaded cells indicate thickness class (Unit: mm)

MLCC - Y5V / Yageo brand

Y5V, 10V to 50V, general purpose


| Y5V - 16V to 50V | | | | | | | | | | | |
|------------------|------------------------------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|
| General purpose | | | | | | | | | | | |
| Capacitance | Last 3 digits of Yageo part number | 16V | | | | 25V | | | 50V | | |
| | | 0402 | 0603 | 0805 | 1206 | 0603 | 0805 | 1206 | 0603 | 0805 | 1206 |
| 10 nF | 103 | 0.5 ±0.05 | | | | 0.8 ±0.07 | | | 0.8 ±0.07 | 0.6 ±0.1 | |
| 22 nF | 223 | | | | | | | | | | |
| 47 nF | 473 | | | | | | | | | | |
| 100 nF | 104 | | | | | | 0.6 ±0.1 | 0.6 ±0.1 | | | 0.6 ±0.1 |
| 220 nF | 224 | | 0.8 ±0.07 | | | | 0.85 ±0.1 | | | 0.85 ±0.1 | |
| 470 nF | 474 | | | 0.85 ±0.1 | | | 1.25 ±0.1 | 0.85 ±0.1 | | | 0.85 ±0.1 |
| 1000 nF | 105 | | | 1.25 ±0.1 | 0.85 ±0.1 | | | 1.15 ±0.1 | | | 1.15 ±0.1 |
| Tape width | | 8mm | | | | | | | | | |

Note: Values in shaded cells indicate thickness class (Unit: mm)

General information

Ordering and packing

Ordering Information:



Thickness classes and packing quantities

| Size Code | Thickness Classification (mm) | Tape Width Quantity Per Reel | 180 mm / 7" | | 330 mm / 13" | | Quantity Per Bulk Case |
|-----------|-------------------------------|------------------------------|-------------|---------|--------------|---------|------------------------|
| | | | Paper | Blister | Paper | Blister | |
| CC0402 | 0.5±0.05 | 8 mm | 10 000 | --- | 50 000 | --- | 50 000 |
| CC0603 | 0.8±0.07 | 8 mm | 4 000 | --- | 15 000 | --- | 15 000 |
| CC0805 | 0.6±0.1 | 8 mm | 4 000 | --- | 20 000 | --- | 10 000 |
| | 0.85±0.1 | 8 mm | 4 000 | --- | 15 000 | --- | 8 000 |
| | 1.25±0.1 | 8 mm | --- | 3 000 | --- | 10 000 | 5 000 |
| CC1206 | 0.6±0.1 | 8 mm | 4 000 | --- | 20 000 | --- | --- |
| | 0.85±0.1 | 8 mm | 4 000 | --- | 15 000 | --- | --- |
| | 1.15±0.1 | 8 mm | --- | 3 000 | --- | 10 000 | --- |
| | 1.6±0.2 | 8 mm | --- | 2 000 | --- | 10 000 | --- |
| CC1210 | 0.6±0.1 | 8 mm | --- | 4 000 | --- | 15 000 | --- |
| | 0.85±0.1 | 8 mm | --- | 4 000 | --- | 10 000 | --- |
| | 1.15±0.1 | 8 mm | --- | 3 000 | --- | 10 000 | --- |
| | 1.15±0.15 | 8 mm | --- | 3 000 | --- | 10 000 | --- |
| | 1.9±0.2 | 8 mm | --- | 2 000 | --- | --- | --- |
| CC1812 | 2.5±0.2 | 8 mm | --- | 1 000 | --- | --- | --- |
| | 0.6/0.85±0.1 | 12 mm | --- | 2 000 | --- | --- | --- |
| | 1.15±0.1 | 12 mm | --- | 1 500 | --- | --- | --- |
| | 1.15±0.15 | 12 mm | --- | 1 500 | --- | --- | --- |
| | 1.6±0.2 | 12 mm | --- | 1 000 | --- | --- | --- |
| | 2.5±0.2 | 12 mm | --- | 1 000 | --- | --- | --- |

Asia

Yageo Taiwan

Tel. +886 (0)2 2917 7555

Fax. +886 (0)2 2917 4286

Yageo China, Dongguan

Tel. +86 769 772 0275

Fax. +86 769 791 0053

Yageo China, Suzhou

Tel. +86 512 825 5568

Fax. +86 512 825 5386

Yageo China, Beijing

Tel. +86 10 851 20810

Fax. +86 10 851 20200

Yageo Hong Kong

Tel. +852 2342 6833

Fax. +852 2342 6588

Yageo Japan

Tel. +81 3 5833 3331

Fax. +81 3 5833 3116

Yageo Korea

Tel. +82 31 712 4797

Fax. +82 31 712 5866

Yageo Malaysia, Penang

Tel. +60 4 397 3317

Fax. +60 4 397 3272

Yageo Malaysia, Kuala Lumpur

Tel. +60 3 5882 2854

Fax. +60 3 5882 8700

Yageo Singapore

Tel. +65-6244 7800

Fax. +65-6244 4943

Europe

Yageo Benelux

Tel. +31 475 385 357

Fax. +31 475 385 589

Yageo Finland

Tel. +358 (0)9 2707 5851

Fax. +358 (0)9 2707 5852

Yageo France

Tel. +33 1 55 51 84 00

Fax. +33 1 55 51 84 24

Yageo Germany / Central Europe

Tel. +49 4121 870-0

Fax. +49 4121 870-271

Yageo Italy / South Europe

Tel. +39 02 2411 301

Fax. +39 02 2411 3051

Yageo UK

Tel. +44 1372 364500

Fax. +44 1372 364567

Yageo Iberia

Tel. +34 93 238 9172

Fax. +34 93 415 9951

Yageo Hungary

Tel. +36-30-3777-441

Fax. +36-94-517-701

Yageo Russia

Tel. +7 501 430 96 27

Fax. +7 095 567 02 66

Yageo Sweden / Nordic

Tel. +46 8 514 933 55

Fax. +46 8 514 933 51

Yageo Czech Republic

Tel. +420-5-43 23 92 33

Fax. +420-5-43 23 92 33

North America

Yageo USA, Seattle

Tel. +1 425 492 2818

Fax. +1 425 492 2819

Yageo USA, Dallas

Tel. +1 972 599 0099

Fax. +1 972 599 0099